

XVS14MMW

Multisound siren, Harmony XVS, prewired, white colour, 0...105dB, 43tones, 240V AC



Main

Range of product	Harmony XVS
Product or component type	Multisound siren
Device short name	XVS

Complementary

Colour	White
Material	PC (polycarbonate): back cover PC (polycarbonate)/ABS (acrylonitrile butadiene-styrene): front PC (polycarbonate)/ABS (acrylonitrile butadiene-styrene): back
Net weight	1.2 kg
Marking	CE
Mounting support	Bracket
Fixing mode	3 holes Ø 9 mm
[Uimp] rated impulse withstand voltage	4 kV
Current consumption	50 mA at 240 V
Electrical connection	Cable: 6.5...8.5 mm, 0.33 mm ² / AWG 22 (signalling circuit) Cable: 6.5...8.5 mm, 0.52 mm ² / AWG 20 (power circuit)
Width	140 mm
Height	114 mm
Depth	223 mm





Environment

Signalling type	43 tones siren
Standards	IEC 61000-6-3 IEC 60947-5-1 EN 60947-01 IEC 61000-6-2
Product certifications	UL
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-10...50 °C
Overvoltage category	Class II conforming to IEC 61140
IP degree of protection	IP53 conforming to IEC 60529
[Us] rated supply voltage	240 V AC
Noise level	0...105 dB (continuous or intermittent tone) at 1 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.5 cm
Package 1 Width	15.5 cm
Package 1 Length	27.5 cm
Package 1 Weight	1.55 kg
Unit Type of Package 2	S04
Number of Units in Package 2	6
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	10.676 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Siren

Dimensions

mm
in.

