

XVS72BMBP

Electronic alarm, Harmony XVS, black, PNP, mounting support DIN 72, 0...90dB, 16tones, 4 channels, 12...24V DC



Main

Range of product	Harmony XVS
Product or component type	Electronic alarm
Device short name	XVS

Complementary

Colour	Black
Material	ABS (acrylonitrile butadiene-styrene): body PC (polycarbonate): terminal cover
Marking	CE
Overvoltage category	Class II conforming to IEC 61140
Mounting support	72 mm DIN rail
[Us] rated supply voltage	12...24 V DC
[Uimp] rated impulse withstand voltage	0.8 kV
Current consumption	117 mA at 12 V 125 mA at 24 V 158 mA at 12 V 200 mA at 24 V
Clamping connection capacity	$\leq 1 \times 1.5 \text{ mm}^2$
Width	72 mm
Height	72 mm
Depth	69.3 mm
Net weight	0.18 kg

Environment

Discrete output type	PNP
Signalling type	16 tones alarm
Standards	UL 464 IEC 61000-6-3 IEC 61000-6-2
Product certifications	UR
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-10...50 °C
IP degree of protection	Panel mounted: IP54 conforming to IEC 60529
Noise level	0...90 dB (continuous or intermittent tone) at 1 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.0 cm
Package 1 Width	9.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	266.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.905 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Electronic Alarm

Dimensions

