


# XVS72BMWP

Electronic alarm, Harmony XVS, white, PNP, 72mm DIN rail, 0...90dB, 16 tones alarm, 4 channels, 12...24V DC



## Main

Range of product	Harmony XVS
Product or component type	Electronic alarm
Device short name	XVS

## Complementary

Colour	White
Material	ABS (acrylonitrile butadiene-styrene): body PC (polycarbonate): terminal cover
Marking	CE
Overvoltage category	Class II conforming to IEC 61140
Mounting support	72 mm DIN rail
[Us] rated supply voltage	12...24 V DC
[Uimp] rated impulse withstand voltage	0.8 kV
Current consumption	117 mA at 12 V 125 mA at 24 V 158 mA at 12 V 200 mA at 24 V
Clamping connection capacity	$\leq 1 \times 1.5 \text{ mm}^2$
Width	72 mm
Height	72 mm
Depth	69.3 mm
Net weight	0.18 kg

## Environment

Discrete output type	PNP
Signalling type	16 tones alarm
Standards	IEC 61000-6-3 IEC 61000-6-2 UL 464
Product certifications	UR
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-10...50 °C
IP degree of protection	Panel mounted: IP54 conforming to IEC 60529
Noise level	0...90 dB (continuous or intermittent tone) at 1 m

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.5 cm
Package 1 Width	9.3 cm
Package 1 Length	9.5 cm
Package 1 Weight	265 g
Unit Type of Package 2	S03
Number of Units in Package 2	16
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	5.164 kg
Unit Type of Package 3	S03
Number of Units in Package 3	16
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	5.164 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------

## Electronic Alarm

### Dimensions

