



Main

Range	MasterPact
Product or component type	Ethernet interface module
Condition of use	With specific accessories
Device application	Communication
Range compatibility	Masterpact (MasterPact MTZ2) circuit breaker Masterpact (MasterPact MTZ3) circuit breaker
Device mounting	Embedded

Complementary

Communication gateway	Ethernet TCP/IP to Modbus
Communication network type	ULP, CANopen on USB Ethernet, Ethernet TCP/IP10/100 Mbps on RJ45
Mounting mode	Drawout
Mounting support	DIN rail
Localisation on device	Chassis
Maximum supply current	3 A
Power consumption in W	72 W
Product certifications	CE FCC EAC
Standards	IEC 60947-6-2 IEC 60950 IACS E10
Height	51 mm
Width	51 mm
Depth	52.5 mm
Net weight	0.075 kg
Web server	Embedded
Provided equipment	1 instruction sheet
Offer type	Spare part

Environment

IP degree of protection	IP30
Ambient air temperature for operation	-20...70 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.85 cm
Package 1 Width	5.25 cm
Package 1 Length	5.1 cm
Package 1 Weight	320.0 g
Unit Type of Package 2	S04
Number of Units in Package 2	8

Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	3.805 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Halogen content performance	Halogen free plastic parts product