

# MVS25H4MW2L

Circuit breaker, EasyPact MVS, 2500A, 65KA,  
4 Poles, MDO, ET2I



## Main

Range	EasyPact
Product name	MVS25H
Device short name	MVS25H
Product or component type	Circuit breaker
Device application	Distribution
Poles description	4P
Protected poles description	4P 4d
[In] rated current	2500 A at 40 °C
Network type	AC
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
Breaking capacity code	H
Suitability for isolation	Yes conforming to IEC 60947-2
Utilisation category	Category B
Trip unit name	ET2I
Trip unit technology	Electronic
Trip unit rating	2500 A

## Complementary

Network frequency	50/60 Hz
Control type	Manually operated
Mounting mode	Drawout
Mounting support	Base plate Rail
Connection position	Vertical Horizontal
Location of connection	Rear
[Ui] rated insulation voltage	1000 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	12 kV conforming to IEC 60947-2
Circuit breaker CT rating	2500 A
Breaking capacity	65 KA Icu at 220...440 V AC 50/60 Hz conforming to IEC 60947-2 50 kA Icu at 690 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] rated service breaking capacity	65 KA (Ics) at 220...440 V AC 50/60 Hz conforming to IEC 60947-2 50 kA (Ics) at 690 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical durability	20000 Cycles (with maintenance) conforming to IEC 60947-2 10000 cycles (without maintenance) conforming to IEC 60947-2
Electrical durability	Category B: 5000 cycles 440 V AC 50/60 Hz without maintenance conforming to IEC 60947-2 Category B: 5000 cycles 690 V AC 50/60 Hz without maintenance conforming to IEC 60947-2
Connection pitch	115 mm without spreader
Contact position indicator	Yes
[Icm] rated short-circuit making capacity	143 KA (Icm) at 220...440 V AC 50/60 Hz conforming to IEC 60947-2 105 kA (Icm) at 690 V AC 50/60 Hz conforming to IEC 60947-2
[Icw] rated short-time withstand current	65 KA (1 s) at 220...440 V AC 50/60 Hz conforming to IEC 60947-2 50 KA (1 s) at 690 V AC 50/60 Hz conforming to IEC 60947-2 50 kA (3 s) at 440/690 V AC 50/60 Hz conforming to IEC 60947-2
Trip unit protection functions	LSI

Protection type	Instantaneous short-circuit protection Overload protection (long time) Short time short-circuit protection
Long time pick-up adjustment type $I_r$	Adjustable 9 settings
Long time pick-up adjustment range	0.4...1 x $I_n$
Long time delay adjustment type	Adjustable 9 settings
[tr] long-time delay adjustment range	0.5...24 s at 6 x $I_r$
Thermal memory	20 minutes before and after tripping
Short-time pick-up adjustment type $I_{sd}$	Adjustable 9 settings
[I <sub>sd</sub> ] short-time pick-up adjustment range	1.5...10 x $I_r$
Short-time delay adjustment type	Adjustable 5 settings
[tsd] short-time delay adjustment range	100...400 ms
Instantaneous pick-up adjustment type $I_i$	Adjustable 9 settings
Instantaneous pick-up adjustment range	2...15 x $I_n$ Off
Zone selective interlocking ZSI	With
Maximum breaking time	25 ms
Maximum closing response time	70 ms
Height	439 mm
Width	556 mm
Depth	395 mm
Net weight	120 kg

## Environment

Standards	IEC 60947-2
Product certifications	IEC[RETURN]EAC
Pollution degree	4 conforming to IEC 60664-1
IP degree of protection	IP40
Ambient air temperature for operation	-5...70 °C
Ambient air temperature for storage	-40...85 °C without control unit -25...85 °C with control unit

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	43.9 cm
Package 1 Width	55.6 cm
Package 1 Length	39.5 cm
Package 1 Weight	120 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>
PVC free	Yes