



Main

Range	ClimaSys
Product name	CU
Product or component type	Cooling unit
Mounting type	Side
Installation	Indoor side
Product destination	For enclosure
Mounting mode	By screws
Supply Voltage	230 V AC at 50/60 Hz, 1 phase
Rated Power	380 W
Cooling power	380 W 50/60 Hz L35-L35 240 W 50/60 Hz L35-L50

Complementary

Height	460 mm
Width	285 mm
Depth	180 mm
[In] rated current	1.6 A
Inrush current	6 A
Power consumption in W	280 W at 50/60 Hz, L35-L35 330 W at 50/60 Hz, L35-L50
Energy efficiency ratio	1.4
Control type	Electronic controller
Temperature setting range	20...55 °C at 50 Hz 20...50 °C at 60 Hz
Ambient air temperature for operation	20...46 °C inside the enclosure: 55 °C maximum: 20...55 °C at 50 Hz outside the enclosure: 20...50 °C at 60 Hz outside the enclosure:
Noise level	60 dB conforming to EN/ISO 3746
Pressure	26 bar
Flow rate	Internal circuit: 280 m3/h at 50/60 Hz External circuit: 280 m3/h at 50/60 Hz
Net weight	17 kg
Cooling gas type	R134a (0.16 kg)
Type of filter	Optional external circuit filter
Protection type	Thermal protection: T 4 A Short-circuit protection (magnetic):
Material	Steel
Colour	Grey (RAL 7035)







Environment

Product certifications	CE
Directives	2006/95/EC - low voltage directive 2004/108/EC - electromagnetic compatibility 2006/42/EC - machinery
Standards	EN 378 EN 60335-2-40 EN 60204-1 EN/ISO 12100 EN 60335-1
IP degree of protection	IP55 conforming to IEC 60529 (on the internal circuit) IP34 conforming to IEC 60529 (on the external circuit)

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18.0 cm
Package 1 Width	28.5 cm
Package 1 Length	46.0 cm
Package 1 Weight	17.0 kg
Unit Type of Package 2	P12
Number of Units in Package 2	16
Package 2 Height	126.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	326.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins