



Main

Product line	QO
Product type	Bar



Complementary






Number of connectors	15
Wire size	AWG 14...AWG 4 copper AWG 12...AWG 4 aluminium
Provided equipment	2 screw
Bar length	143 mm
Maximum length of segment	80 mm
Device mounting	Direct mounting back of enclosure
Height	11.10 Mm 11.10 mm
Depth	7.92 Mm 7.92 mm
Tightening torque	: 30 lb.in Mounting screw: 30 lb.in : 20 lb.in, AWG 14...AWG 10, copper : 20 lb.in, AWG 12...AWG 10, aluminium : 25 lb.in, AWG 8 : 35 lb.in, AWG 6...AWG 4 : 25 lb.in, AWG 14...AWG 12, copper : 25 lb.in, AWG 12...AWG 10, aluminium

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.032 cm
Package 1 Width	1.27 cm
Package 1 Length	14.478 cm
Package 1 Weight	68.039 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.906 cm
Package 2 Width	16.002 cm
Package 2 Length	18.542 cm
Package 2 Weight	775.643 g
Unit Type of Package 3	PAL
Number of Units in Package 3	2160
Package 3 Height	71.12 cm

Package 3 Width	101.6 cm
Package 3 Length	121.92 cm
Package 3 Weight	186.426 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------