

# ZB4BVB1

Complete body light block assembly, Harmony XB4, metal, universal LED, body fixing collar, 24V AC DC



## Main

|                               |  |
|-------------------------------|--|
| Range of product              | Harmony XB4  |
| Product or component type     | Complete body/light block assembly   |
| Device short name             | ZB4  |
| Fixing collar material        | Zamak  |
| Sale per indivisible quantity | 1  |
| Connections - terminals       | Screw clamp terminals, $\leq 2 \times 1.5 \text{ mm}^2$ with cable end<br>Screw clamp terminals, $\geq 1 \times 0.22 \text{ mm}^2$ without cable end |
| Light source                  | Universal LED  |
| Bulb base                     | Integral LED   |
| Light source colour           | White  |
| [Us] rated supply voltage     | 24 V AC/DC at 50/60 Hz   |

## Complementary

|  |   |
|--|---|
| CAD overall width                      | 30 mm   |
| CAD overall height                     | 47 mm   |
| CAD overall depth                      | 37 mm   |
| Terminals description ISO n°1          | (X1-X2)PL   |
| Net weight                             | 0.054 kg  |
| Tightening torque                      | 0.8...1.2 N.m conforming to IEC 60947-1   |
| Shape of screw head                    | Cross compatible with Philips no 1 screwdriver<br>Cross compatible with pozidriv No 1 screwdriver<br>Slotted compatible with flat $\varnothing 4 \text{ mm}$ screwdriver<br>Slotted compatible with flat $\varnothing 5.5 \text{ mm}$ screwdriver |
| [Ui] rated insulation voltage          | 600 V (pollution degree 3) conforming to IEC 60947-1  |
| [Uimp] rated impulse withstand voltage | 6 kV conforming to IEC 60947-1  |
| Signalling type                        | Steady  |
| Supply voltage limits                  | 19.2...30 V DC<br>21.6...26.4 V AC  |
| Current consumption                    | 18 mA   |
| Service life                           | 100000 h at rated voltage and 25 °C   |
| Surge withstand                        | 1 kV conforming to IEC 61000-4-5  |
| Device presentation                    | Basic sub-assemblies  |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.






## Environment

|                                       |  |
|---------------------------------------|--|
| Protective treatment                  | TH   |
| Ambient air temperature for storage   | -40...70 °C  |
| Ambient air temperature for operation | -40...70 °C  |
| Electrical shock protection class     | Class I conforming to IEC 60536  |
| Standards                             | IEC 60947-1<br>JIS C8201-5-1<br>IEC 60947-5-1<br>UL 508<br>CSA C22.2 No 14<br>IEC 60947-5-5<br>IEC 60947-5-4<br>JIS C8201-1  |
| Product certifications                | LROS (Lloyds register of shipping)[RETURN]GL[RETURN]UL listed[RETURN]DNV[RETURN]CSA[RETURN]BV  |
| Vibration resistance                  | 5 gn (f= 2...500 Hz) conforming to IEC 60068-2-6   |
| Shock resistance                      | 30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27<br>50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27 |
| Resistance to fast transients         | 2 kV conforming to IEC 61000-4-4   |
| Resistance to electromagnetic fields  | 10 V/m conforming to IEC 61000-4-3   |
| Resistance to electrostatic discharge | 6 KV on contact (on metal parts) conforming to IEC 61000-2-6<br>8 kV in free air (in insulating parts) conforming to IEC 61000-2-6   |
| Electromagnetic emission              | Class B conforming to IEC 55011  |

## Packing Units

|                              |            |
|------------------------------|------------|
| Unit Type of Package 1       | PCE        |
| Number of Units in Package 1 | 1          |
| Package 1 Height             | 5.600 cm   |
| Package 1 Width              | 3.400 cm   |
| Package 1 Length             | 5.400 cm   |
| Package 1 Weight             | 52.000 g   |
| Unit Type of Package 2       | S03        |
| Number of Units in Package 2 | 200        |
| Package 2 Height             | 30.000 cm  |
| Package 2 Width              | 30.000 cm  |
| Package 2 Length             | 40.000 cm  |
| Package 2 Weight             | 10.837 kg  |
| Unit Type of Package 3       | P06        |
| Number of Units in Package 3 | 1600       |
| Package 3 Height             | 75.000 cm  |
| Package 3 Width              | 60.000 cm  |
| Package 3 Length             | 80.000 cm  |
| Package 3 Weight             | 100.084 kg |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           |  <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)  |
| Mercury free               | Yes   |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information |  <a href="#">Yes</a>                           |
| Environmental Disclosure   |  <a href="#">Product Environmental Profile</a> |
| Circularity Profile        |  <a href="#">End Of Life Information</a>       |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins       |

## Contractual warranty

---


|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

---

---

Dimensions

---



Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

| Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board   | Connection by Faston Connectors  |
|---|--|
|    |  |
| <p>(1) Diameter on finished panel or support<br/>                 (2) 40 mm min. / 1.57 in. min.<br/>                 (3) 30 mm min. / 1.18 in. min.<br/>                 (4) <math>\varnothing 22.5 \text{ mm} / 0.89 \text{ in.}</math> recommended (<math>\varnothing 22.3 \text{ mm}_0^{+0.4} / 0.88 \text{ in.}_0^{+0.016}</math>)<br/>                 (5) 45 mm min. / 1.78 in. min.<br/>                 (6) 32 mm min. / 1.26 in. min.</p> |  |