



### Main

Range	Acti9
Product or component type	Terminal block
Device application	Connection

### Complementary

Range compatibility	Acti 9 Acti9 DB TNA chassis Acti 9 Acti9 DB PEV chassis
[Ie] rated operational current	125 A
[Ui] rated insulation voltage	500 V
Poles description	1P
[Uimp] rated impulse withstand voltage	6 kV
Width	18 mm
Cable stiffness	Flexible 35 mm <sup>2</sup> Solid 50 mm <sup>2</sup>
Ambient air temperature for storage	-40...85 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	7.000 cm
Package 1 Length	9.000 cm
Package 1 Weight	77.500 g
Unit Type of Package 2	S02
Number of Units in Package 2	52
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.290 kg
Unit Type of Package 3	P12
Number of Units in Package 3	832
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	80.640 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product