

XVMC33

Harmony XVM, Illuminated unit for modular tower lights, plastic, green, Ø45, for bulb BA 15d, <= 230 V AC/DC



Main

| | |
|------------------------------------|---|
| Range of product | Harmony XVM |
| Product or component type | Indicator bank |
| Beacon or indicator bank unit type | Illuminated unit |
| Component name | XVM |
| Light source | Bulb not included, green |
| Bulb type | Incandescent with BA 15d base Super bright LED Flash discharge tube |
| [Us] rated supply voltage | <= 230 V AC/DC |

Complementary

| | |
|--|--|
| Mounting diameter | 45 mm |
| Assembly style | Customer assembly |
| Maximum power dissipation in W | 5 W |
| Connections - terminals | Screw terminals, 1 x 0.325...1 x 1.5 mm ² |
| Marking | CE |
| [Ui] rated insulation voltage | 250 V conforming to IEC 60947-1 |
| Nominal voltage limit | 0.85...1.1 Un conforming to IEC 60947-5-1 |
| [Uimp] rated impulse withstand voltage | 4 kV conforming to IEC 60947-1 |
| Luminance | 650 cd/m ² |
| CAD overall width | 47 mm |
| CAD overall height | 65 mm |
| CAD overall depth | 47 mm |
| Net weight | 0.04 kg |

Environment

| | |
|---------------------------------------|---|
| Product certifications | CCC |
| Standards | IEC 60947-1 IEC 60947-5-1 |
| Ambient air temperature for storage | -25...70 °C |
| Ambient air temperature for operation | -10...50 °C |
| IP degree of protection | IP40 any position except vertical position conforming to IEC 60529 IP42 vertical position conforming to IEC 60529 |
| Electrical shock protection class | Class I aluminium tube mounting conforming to IEC 60947-1 Class I aluminium tube mounting conforming to IEC 60947-5-1 Class I aluminium tube mounting conforming to IEC 61140 Class II base mounting conforming to IEC 60947-1 Class II base mounting conforming to IEC 60947-5-1 Class II base mounting conforming to IEC 61140 |
| Protective treatment | TC |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 5.100 cm |
| Package 1 Width | 6.800 cm |
| Package 1 Length | 10.400 cm |
| Package 1 Weight | 45.000 g |
| Unit Type of Package 2 | S01 |
| Number of Units in Package 2 | 25 |
| Package 2 Height | 15.000 cm |
| Package 2 Width | 15.000 cm |
| Package 2 Length | 40.000 cm |
| Package 2 Weight | 1.433 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |


Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Customer Assembled Tower Light

Dimensions

Below drawing shows a tower light with 3 illuminated stages. Select the number of stages according to the product characteristics in order to get b dimension.



- (1) Cover (included with base unit XVMC21/C29•)
- (2) Illuminated unit
- (3) Base unit XVMC21 (without buzzer) or XVMC29• (with buzzer), to be ordered separately
- (4) Fixing base XVMZ0•/Z0•T, to be ordered separately

| Number of illuminated units (ref. 2) | b in mm | b in in. |
|--------------------------------------|---------|----------|
| 1 | 127 | 5.00 |
| 2 | 192 | 7.56 |
| 3 | 257 | 10.12 |
| 4 | 322 | 12.68 |
| 5 | 387 | 15.24 |