

## Product data sheet

### Characteristics

# XY2CD111

## SIMPLE CABLE PULL SWITCH 240VAC 10A

### XY2CD



#### Main

Range of product	Telemecanique Emergency stop rope pull switches XY2C
Product or component type	Simple rope pull switch
Device short name	XY2CD
Housing colour	Blue
Overvoltage category	Class I conforming to IEC 61140 Class I conforming to NF C 20-030

#### Complementary

Trigger cable maximum length	6 m
Body material	Zamak
Head material	Plastic
[Us] rated supply voltage	240 V
Contacts type and composition	1 NC + 1 NO
Contact operation	Snap action
Resistance to wrenching	237 DaN operating head 36 daN operating ring
Cable entry number	3 3 entries tapped for Pg 11 cable gland for Pg 11
Mechanical durability	1500000 cycles
[Ie] rated operational current	3 A at 240 V, AC-15, A300 conforming to IEC 60947-5-1 appendix A 0.27 A at 250 V, DC-13, Q300 conforming to IEC 60947-5-1 appendix A
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	400 V (pollution degree 3) conforming to IEC 60947-1 300 V conforming to UL 508 300 V conforming to CSA C22.2 No 14
Compatibility code	XY2CD

#### Environment



Product certifications	CCC[RETURN]CE
Ambient air temperature for operation	-20...70 °C
IP degree of protection	IP66 conforming to IEC 60529

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.200 cm
Package 1 Width	6.500 cm
Package 1 Length	14.600 cm
Package 1 Weight	285.000 g
Unit Type of Package 2	S01

Number of Units in Package 2	16
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	4.745 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
Circularity Profile	No need of specific recycling operations