



Main

Range of product	Acti9
Product name	Acti9 IHH
Device short name	IHH
Product or Component Type	Mechanical time switch
Number of channels	1
Function Available	Manual time changeover

Complementary

Device Application	Building
Load type	Parallel-corrected fluorescent tube 5 x 58 W 4.7 µF Parallel-corrected fluorescent tube 7 x 40 W 7 µF Parallel-corrected fluorescent tube 2 x 100 W 18 µF 230 V AC halogen lamp 1000 W 230 V AC incandescent lamp 1000 W Fluocompact lamp 700 VA Compact fluorescent lamp 150 W LED lamp < 2 W 30 W LED lamp > 2 W 300 W
Cycle duration	7 days
Maximum number of switchings	42 on - 42 off
Minimum interval duration	2 h
Type of setting	Manual time changeover
Measurement accuracy	+/- 1 s/day 68 °F (20 °C)
Power consumption in W	0.5 W
Maximum switching current	16 A - 250 V AC 1 4 A - 250 V AC 0.6
[Ue] rated operational voltage	230...240 V AC 50-60 Hz
Battery Life	10 year(s)
Backup time	150 h time and program saving
Mounting Support	DIN rail
9 mm pitches	2
Colour tint	White RAL 9003)
Connections - terminals	Screw terminals
Width	0.71 in (18 mm)
Height	3.54 in (90 mm)
Depth	2.60 in (66 mm)
Net Weight	0.22 lb(US) (0.101 kg)

Environment

Ambient air temperature for operation	14...122 °F (-10...50 °C)
IP degree of protection	Terminals IP20 B

Ordering and shipping details

Category	US10DE200908
Discount Schedule	0DE2
GTIN	3303430153313
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.79 in (2.0 cm)
Package 1 Width	2.76 in (7.0 cm)
Package 1 Length	3.94 in (10.0 cm)
Package 1 Weight	3.14 oz (89.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	100
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	20.84 lb(US) (9.452 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------