



Main

Range	ComPacT
Range of Product	ComPacT NS630b...1600 new generation ComPacT NS1600b...3200 new generation
Device short name	MN
Product or Component Type	Voltage release
Device Application	Control
Voltage release type	Opening coil Undervoltage release
Control Type	Standard
[Uc] control circuit voltage	24 V AC 50/60 Hz 24...30 V DC
Circuit breaker mounting mode	Fixed
Range compatibility	ComPacT ComPacT NS630b...1600 ComPacT ComPacT NS1600b...3200

Complementary

Operating threshold	0.35...0.7 x Un opening 0.85 x Un closing
Response time	90 ms +/- 5 % Compact NS630b...1600 90 ms +/- 5 % Compact NS1600b...3200 40 ms +/- 5 % MasterPact NT 90 ms +/- 5 % MasterPact NW
Supply holding power	4.5 W
Accessory / separate part category	Spare part MasterPact NT Spare part MasterPact NW Spare part ComPacT NS630b...1600 new generation Spare part ComPacT NS1600b...3200 new generation

Ordering and shipping details

Category	US10DE201250
Discount Schedule	0DE2
GTIN	3303430336686
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.38 in (3.5 cm)
Package 1 Width	2.36 in (6.0 cm)
Package 1 Length	3.23 in (8.2 cm)
Package 1 Weight	5.43 oz (154.0 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	3.54 in (9.0 cm)
Package 2 Width	5.12 in (13.0 cm)

Package 2 Length	7.28 in (18.5 cm)
Package 2 Weight	3.53 lb(US) (1.6 kg)
Unit Type of Package 3	S03
Number of Units in Package 3	20
Package 3 Height	11.81 in (30.0 cm)
Package 3 Width	11.81 in (30.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	7.94 lb(US) (3.6 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------