

6340AXXMDS-DC3

Relay, SE Relays, solid state, SPST NO, 40A,
3V to 200V DC, 3V to 32V DC U_c, MOSFET
DC switching, screw terminal



Main

Range	Legacy
Product Type	Solid state relay
Maximum output current	40 A DC
Mounting Support	Panel
Network Number of Phases	1 phase
Output Voltage	3...200 V DC
Control Circuit Voltage	3.5...32 V DC

Complementary

Input Impedance	1 kOhm
Holding Current	20 mA
Input Current Limits	10 mA DC typical
Switch Function	SPST
Contacts Type and Composition	NO
Protection Technology	Current limiter
Tightening Torque	10 lb.in for input 20 lb.in for output
Connections Terminals	Input screw clamp terminal, 1 Output screw clamp terminals, 1
Screw Type	M3.5 M6
Local Signalling	For input status 1 LED (green)
Switching Device	Mosfet output DC switching
Maximum Peak Voltage	200 V
Surge Current	90 A 16.6 ms
Must Release Voltage	1 V
Voltage Drop	<2.8 V on-state DC
Power Factor	1 with maximum load
Insulating Resistance	1 GΩ
Thermal Resistance	1.06 °C/W
Leakage Current	8 mA at off-state
Response Time	600 μs (turn-on) 2.6 ms (turn-off)
Dielectric Strength	2500 V between input and ground 2500 V between output and ground 2500 V between input and output
Height	1.39 in (35.3 mm)
Width	1.85 in (47.1 mm)
Depth	2.30 in (58.4 mm)
Product Weight	4.76 oz (135 g)

Environment

Product Certifications	UL[RETURN]CSA[RETURN]CE
IP Degree of Protection	IP20
Ambient Air Temperature for Operation	-40...176 °F (-40...80 °C)
Ambient Air Temperature for Storage	-40...212 °F (-40...100 °C)


Ordering and shipping details

Category	US10CP221127
Discount Schedule	0CP2
GTIN	3606480277412
Returnability	No
Country of origin	IN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.90 in (4.83 cm)
Package 1 Width	2.60 in (6.6 cm)
Package 1 Length	1.90 in (4.83 cm)
Package 1 Weight	0.33 lb(US) (0.15 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Connections and Wiring Diagrams

