



#### Main

Product Range	Legacy
Product Type	Socket
Product Compatibility	Relay 788XBXR/XCXR
Number of Terminals	11
Switch Function	3PDT
Contact Composition	3 NO + 3 NC

#### Complementary

Rated Current	15 A
[Ue] rated operational voltage	300 V
Contact Terminal Arrangement	Mixed
Connections Terminals	Pin pins for printed circuit board, clamping connection capacity:1 mm <sup>2</sup> , AWG 16 solid for output Panel pins for printed circuit board, clamping connection capacity:1 mm <sup>2</sup> , AWG 16 stranded for output
Fixing Mode	By screws printed circuit boards
Product Weight	0.43 oz (12.1 g)
Width	1.50 in (38.1 mm)
Depth	1.37 in (34.8 mm)

#### Environment

Ambient Air Temperature for Storage	-40...221 °F (-40...105 °C)
Ambient Air Temperature for Operation	-40...131 °F (-40...55 °C)
IP Degree of Protection	IP20
Flame Retardance	UL94-V0
Product Certifications	UL[RETURN]CSA[RETURN]CE

#### Ordering and shipping details

Category	US10CP221127
Discount Schedule	OCP2
GTIN	3606480277801
Returnability	Yes
Country of origin	TW

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.37 in (3.47 cm)
Package 1 Width	1.50 in (3.81 cm)
Package 1 Length	0.47 in (1.201 cm)
Package 1 Weight	0.43 oz (12.1 g)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

**16-1351 Metal Hold-Down Clip**  
See Section 3 p. 10-11

**70-178-1**

**70-178-2**

**RECOMMENDED CIRCUIT BOARD LAYOUT BOTTOM VIEW**

1 2 3 N.C.  
4 5 6 N.O.  
7 8 9 COM  
A B INPUT

NEMA IEC

0.078 [1.98] DIA. ELEVEN PLACES  
0.156 [3.9] DIA HOLES