

861HSSR210-AC-1

Relay, SE Relays, solid state, SPST NO, 10A, 24 to 280 VAC, 90 to 208 VAC, SCR, AC zero cross, hazardous locations approved



Main

Range	Legacy
Product Type	Solid state relay
Maximum output current	10 A AC
Mounting Support	Panel DIN rail
Network Number of Phases	1 phase
Output Voltage	3...150 V DC
Control Circuit Voltage	90...280 V AC

Complementary

Holding Current	50 mA
Input Current Limits	20 mA at 240 V AC typical
Switch Function	SPST
Contacts Type and Composition	NO
Tightening Torque	0.8 N.m for input/output
Connections Terminals	Input/output screw clamp terminal 0.00 in ² (2.5 mm ²) AWG 14)
Local Signalling	For input status 1 LED (green)
Switching Device	SCR output Zero voltage switching
Load Current	10 A at nominal load 8 A incandescent lamp 4.5 A motor
Overload Current	24 A for 1 second
Surge Current	500 A 1 cycle
Must Release Voltage	10 V
Voltage Drop	<1.6 V peak AC <1.25 V on-state AC
Thermal Resistance	0.66 °C/W
Maximum I ² t for fusing	1250 A ² .s 8.3 ms
Leakage Current	6 mA at off-state 240 V AC
DV/dt	500 V/μs off-state at maximum rated voltage
Response Time	40 ms (turn-off) 40 ms (turn-on)
Dielectric Strength	4000 V between input and output 2500 V between terminals and chassis
Height	2.56 in (65 mm)
Width	0.62 in (15.75 mm)
Depth	3.54 in (89.93 mm)
Product Weight	4.48 oz (127.1 g)
Device Presentation	Complete device

Environment

Product Certifications	CE[RETURN]CSA[RETURN]UL
IP Degree of Protection	IP20
Ambient Air Temperature for Operation	-22...176 °F (-30...80 °C)
Ambient Air Temperature for Storage	-40...212 °F (-40...100 °C)


Ordering and shipping details

Category	US10CP222375
Discount Schedule	0CP2
GTIN	3606480282133
Returnability	Yes
Country of origin	IN


Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.64 in (9.24 cm)
Package 1 Width	0.69 in (1.76 cm)
Package 1 Length	2.56 in (6.5 cm)
Package 1 Weight	4.48 oz (127.1 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Approximate Dimensions



Connections and Wiring Diagrams

