


## 8736SCO7V02H309S

NEMA starter, Type S, reversing, vertical, Size 1, 27A, 10HP at 575VAC, up to 100kA SCCR, 3 phase, 3 pole, Motor Logic SSOLR, 120VAC coil, open



### Main

Product Type	Starter
Product Range	S
Starter Type	Reversing

### Complementary

NEMA Size	1
Rated Current	27 A
Number of Poles	3P
Mounting Orientation	Vertical
Wiring Mode	3 wires
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type of Overload	Solid state Motor Logic class 10/20
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
SCCR	Circuit-breaker 70 A maximum: 100 kA at 480 V AC Fuse J 60 A maximum: 100 kA at 600 V AC Fuse T 60 A maximum: 100 kA at 600 V AC Fuse RK1 60 A maximum: 100 kA at 600 V AC Fuse RK5 60 A maximum: 100 kA at 600 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Terminal Type	Screw clamp terminals
Height	11.52 in (292.61 mm)
Width	5.47 in (138.94 mm)
Depth	5.31 in (134.87 mm)

### Environment

Enclosure Type	Not rated (open device)
Certifications	UL Listed[RETURN]CSA


## Ordering and shipping details

Category	US10CP121272
Discount Schedule	0CP1
GTIN	785901508434
Returnability	No
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.70 in (22.098 cm)
Package 1 Width	11.60 in (29.464 cm)
Package 1 Length	13.70 in (34.798 cm)
Package 1 Weight	10.84 lb(US) (4.917 kg)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Not compliant
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------