



#### Main

Product	Mechanically Held Lighting Contactor
Type	S

#### Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Current Rating	100 A
Number of Poles	3P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Electrical Connection	Lugs
Height	7.24 in (184 mm)
Depth	6.73 in (171 mm)
Width	5.94 in (151 mm)

#### Environment

Enclosure Type	Not rated (open device) surface none
Product Certifications	UL Listed[RETURN]CSA

#### Ordering and shipping details

Category	US10CP121324
Discount Schedule	0CP1
GTIN	785901102427
Returnability	Yes
Country of origin	MX

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.60 in (24.384 cm)
Package 1 Width	13.70 in (34.798 cm)
Package 1 Length	17.80 in (45.212 cm)
Package 1 Weight	18.15 lb(US) (8.233 kg)

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Not compliant
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

Contractual warranty

Warranty	18 months
----------	-----------