

8940XD4S2V06A28H30

Pump Panel, NEMA Type S, Well Guard, oil field, Size 2, 45A, 25HP, HLL36050M72 circuit breaker, Motor Logic SSOLR, 480VAC 60Hz coil, NEMA 3R



Main

Product	Well-Guard Control
Type	S2
Device Application	Pumping

Complementary

Control Circuit Type	Common control circuit
Control Circuit Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Line Rated Current	45 A
Number of Poles	3
Horsepower Rating	25 hp 480 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO) Push-button START)
Disconnect Type	Associated circuit breaker
Circuit breaker CT rating	50 A
Circuit breaker type	HLL
Thermal overload type	Motor Logic solid state class 10/20
Protection Type	Overload Phase loss Phase unbalance
Device mounting	Surface
Electrical Connection	Screw terminal
NEMA size	2
Height	38.50 in (978 mm)
Width	20.43 in (519 mm)
Depth	9.41 in (239 mm)

Environment

NEMA Rating	NEMA 3R
Enclosure type	Weatherproof enclosure indoor/outdoor
Product Certifications	UL Listed[RETURN]NEMA


Ordering and shipping details

Category	US10CP121395
Discount Schedule	0CP1
GTIN	785901226932
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	38.50 in (97.8 cm)
Package 1 Width	20.43 in (51.9 cm)
Package 1 Length	9.41 in (23.9 cm)
Package 1 Weight	100.00 lb(US) (45.359 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------