

### Main

Range	Acti9
Device short name	MSC 18
Product or Component Type	Chassis
Device Application	Distribution

### Complementary

Range compatibility	Acti 9 Acti9 Isobar B distribution board
Line Rated Current	250 A
Short-circuit withstand	25 kA 0.1 s
[Icw] rated short-time withstand current	25 kA
[Ui] Rated Insulation Voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Number of ways	1 way incomer) - 3P 12 ways outgoer)
Outgoer Pole capacity	12 x 0.71 in (18 mm)
Length	4.33 in (110 mm)
Width	8.46 in (215 mm)


### Ordering and shipping details

Category	US10DE200908
Discount Schedule	0DE2
GTIN	9321243001069
Returnability	No
Country of origin	FR

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.74 in (9.5 cm)
Package 1 Width	9.45 in (24.0 cm)
Package 1 Length	15.55 in (39.5 cm)
Package 1 Weight	2.95 lb(US) (1.34 kg)

### Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------