

## Main

Range	Acti9
Device short name	MSC 18
Product or Component Type	Chassis
Device Application	Distribution

## Complementary

Range compatibility	Acti 9 Acti9 IsoBar B distribution board
Line Rated Current	250 A
[Icw] rated short-time withstand current	25 kA
Number of ways	1 way incomer) - 3P 48 ways outgoer)
Outgoer Pole capacity	48 x 0.71 in (18 mm)
Location of Feed	Top
Length	17.09 in (434 mm)
Width	8.46 in (215 mm)


## Ordering and shipping details

Category	US10DE200908
Discount Schedule	0DE2
GTIN	9321245853192
Returnability	No
Country of origin	AU

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	11.00 lb(US) (4.990 kg)

## Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------