

QC816D400SL

Meter mains, QO, CSED, ringless socket,
400A, surface mount, maximum 8 spaces, 16
circuits, Class 320 with lever bypass



Main

Product or Component Type	Meter Mains
Range of Product	QO
Includes	Circuit-breaker 1) 200 A 240 V AC

Complementary

Line Rated Current	400 A
Meter socket type	Ringless
Mounting	Surface
Number of spaces	8
Number of circuits	16
Wire Size	AWG 4...600 kcmil 1 aluminium/copper AWG 1/0...350 kcmil 2 aluminium/copper
Disconnect	Service disconnect (ordered separately)
Service feed location	OH UG
Bypass type	Class 320 Lever bypass
Height	32.68 in (830 mm)
Width	28.27 in (718 mm)
Depth	7.91 in (201 mm)
Bus Rating	200.0 A

Environment

NEMA Degree of Protection	NEMA 3R
Product certifications	UL listed file E-6294

Ordering and shipping details

Category	US1DE3A00022
Discount Schedule	DE3A
GTIN	785901127284
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.90 in (20.066 cm)
Package 1 Width	28.30 in (71.882 cm)
Package 1 Length	30.70 in (77.978 cm)
Package 1 Weight	77.00 lb(US) (34.927 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	5
Package 2 Height	43.00 in (109.22 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	420.38 lb(US) (190.68 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations