

SE8350U0B00

Low-Voltage Fan Coil Room Controller &
Zone Controller: BACnet MS/TP, RH sensor &
control, Silver Case/Fascia





Main

Device Application	Low voltage fan coil
Net Weight	11.99 oz (340 g)
Product or Component Type	Room controller
Product name	SE8000 Series
Device short name	SE8300
Height	4.72 in (120 mm)
AWG Gauge	AWG 24...AWG 18
Targeted region	North America.
Directives	2014/30/EU - electromagnetic compatibility 2014/35/EU - low voltage directive 2014/53/EU - radio equipment directive
Humidity Measurement Drift	Less Than 1 % Yearly
Line Rated Current	4 A
Width	3.39 in (86 mm)
Temperature Resolution	0.1 °C
Market Segment	Lodging/Hotel Small commercial Buildings Healthcare Non-critical buildings Office Residential School
Housing Colour	Silver
Ambient Air Temperature for Storage	-22...122 °F (-30...50 °C)
Depth	0.98 in (25 mm)
Ambient air temperature for operation	32...122 °F (0...50 °C)
Measurement accuracy	Temperature +/- 0.5 °C, Humidity +/- 5 %, 20...80 % RH non-condensing) Humidity +/- 10 %, 10...20 % non-condensing) Humidity +/- 10 %, 80...90 % non-condensing)
Information displayed	Temperature - 40...122 °F
Network frequency	50 Hz 60 Hz
Communication Port Protocol	BACnet MS/TP Modbus RTU
Input voltage	0...10 V DC
Temperature Setting Range	54...100 °F (12...37.5 °C) cooling 40...90 °F (4.5...32 °C) heating
Calibration Certificate	1 Pt
Output voltage	24 V AC relay output 0...10 V DC analog output
Relative Humidity	0...95 %
Output Current	1 A relay output 3 A relay output inrush) 0.3 A universal output 1.5 A universal output inrush)
Input type	Dry contact 2 Analog 5
Sensor Type	10 kOhm T2 NTC thermistor Temperature Space RH sensor Humidity Bulk polymer Humidity
Output type	5 xrelay output 4 xuniversal
[Us] rated supply voltage	24 V AC 50/60 Hz +/- 15 %

Standards	EN/IEC 60730-1 FCC part 15 Subpart B ICES-003 ETSI EN 300 328 ETSI EN 301 489-1:v1.9.2 FCC part 15 Subpart C UL 60730-2-9 ETSI EN 301 489-17:v2.2.1, 2012
Humidity setting range	30...95 %
Range	EcoStruxure Building Expert
Economizer	Yes
Humidity Control	Yes
PIR Cover	No
Scheduling	No

Complementary

Surface treatment	Untreated
Surface Finish	Matte
Function available	Fan control HVAC control Available with CO2/RH/T Brightness sensor Changes can be made directly over display Code lock function Easily configurable Firmware update by USB

Ordering and shipping details

Category	US1DE1021009
Discount Schedule	DE10
GTIN	3606480770050
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.89 in (4.8 cm)
Package 1 Width	4.21 in (10.7 cm)
Package 1 Length	6.06 in (15.4 cm)
Package 1 Weight	17.64 oz (500 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: LEAD, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information