

TDRPRO-5102

Time delay relay, Harmony SE Relays, DPDT,
100ms to 9990hours, 7time scales, 3 functions,
socket compatible, 12A, 12...240V AC/DC



Main

Product Range	Legacy
Product or Component Type	Time delay relay
Switch Function	DPDT
Contacts Material	Silver alloy contacts
Time Delay Type	Multifunction
Setting-up	Thumbwheel
Rated Supply Voltage	12...240 V AC/DC 50...60 Hz

Complementary

Time Delay Range	100 ms...9990 hr in steps of 0.1 s 100 ms...9990 hr in steps of 1 second 100 ms...9990 hr in steps of 0.1 min 100 ms...9990 hr in steps of 1 min 100 ms...9990 hr in steps of 0.1 h 100 ms...9990 hr in steps of 1 h 100 ms...9990 hr in steps of 10 h
Operating Time	25 ms
Brake Release Time	25 ms
Control Type	Dial front
Voltage Range	0.85...1.15 Un 0.85...1.15 Un 0.85...1.15 Un 0.85...1.15 Un 0.85...1.15 Un 0.85...1.15 Un 0.85...1.15 Un 0.85...1.15 Un 0.85...1.15 Un 0.85...1.15 Un
Nominal Output Current	12 A
Local Signalling	1 LED red, blinking timing in progress 1 LED per input green
Repeat Accuracy	+/- 0.1 % of the measuring range
Reset Time	150 ms maximum
Power Consumption in VA	2.5 VA 12...240 V
Power Consumption in W	2 W 12...240 V
Rated Operational Current	12 A at 120 V AC (on resistive load) 12 A at 240 V AC (on resistive load) 12 A at 30 V DC (on resistive load)
Motor Power HP	1 Hp 240 V AC 0.5 hp 120 V AC
Electrical Durability	100000 cycles
Mechanical Durability	10000000 cycles
Mounting Support	Socket
Height	2.83 in (71.95 mm)
Width	1.89 in (48 mm)
Depth	1.88 in (47.8 mm)
Product Weight	4.23 oz (120 g)

Environment

Dielectric Strength	2500 V between input and output
Standards	IEC 61810-1
Product Certifications	UL
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
Ambient Air Temperature for Operation	14...131 °F (-10...55 °C)
IP Degree of Protection	IP40 IEC 60529 enclosure)





Ordering and shipping details

Category	US10CP221127
Discount Schedule	0CP2
GTIN	3606480283086
Returnability	Yes
Country of origin	CZ


Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.40 in (6.1 cm)
Package 1 Width	2.40 in (6.1 cm)
Package 1 Length	4.20 in (10.67 cm)
Package 1 Weight	0.35 lb(US) (0.16 kg)
Unit Type of Package 2	CAR
Number of Units in Package 2	100
Package 2 Height	12.60 in (32 cm)
Package 2 Width	9.06 in (23 cm)
Package 2 Length	23.62 in (60 cm)
Package 2 Weight	32.63 lb(US) (14.8 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Approximate Dimensions



Connections and Wiring Diagrams

