



## Main

Range	Acti 9
Range of product	Acti 9 iEM3000
Device short name	IEM3355
Product or Component Type	Energy meter

## Complementary

Poles description	3P + N 1P + N 3P
Type of measurement	Active and reactive energy Active and reactive power Current Voltage
Metering type	Active, reactive, apparent energy (signed, four quadrant)
Device Application	Multi-tariff Sub billing Partial meter
Accuracy class	Class 1 active energy IEC 62053-21 Class 1 active energy IEC 61557-12 Class B active energy EN 50470-3
Input type	Direct input
Line Rated Current	125 A
Rated voltage	100...277 V 173...480 V
Network Frequency	50 Hz 60 Hz
Technology Type	Electronic
Display Type	LCD display
Sampling rate	32 samples/cycle
Measurement current	0...125 A
Maximum value measured	99999999.9 kWh
Tariff input	Tariff 4)
Communication port protocol	Modbus RTU 9.6, 19.2 and 38.4 kbauds even/odd or none 4000 V
Communication port support	Screw terminal block RS485
Local signalling	Green indicator light power ON Yellow flashing LED accuracy checking Alarm overload Yellow indicator light communications are active on the Modbus port (Modbus)
Number of inputs	1 digital 0...5 V/11...40 V 24 V DC
Number of Outputs	1 digital (static)
Output voltage	5...40 V DC@50 mA
Mounting Mode	Clip-on
Mounting Support	DIN rail
Connections - terminals	Screw terminals 0.08 in <sup>2</sup> (50 mm <sup>2</sup> )

Overvoltage category	III
Standards	IEC 61010 IEC 61036 IEC 61557-12 IEC 62053-23 UL 61010-1 IEC 62053-21
Product certifications	CE IEC 61010 safety) CE EN 61557-12 power monitor) CE IEC 61326-1 EMC) CULus UL 61010 safety) CULus ANSI C12.20 sub-meter) EAC sub-meter) RCM NMI M 6-1 sub-meter) UL MID EN 50470-3 sub-meter) MID EN 62052 sub-meter)

## Environment

IP degree of protection	Front panel IP40 IEC 60529 Body IP20 IEC 60529
Pollution degree	2
Relative humidity	5...95 % 122 °F (50 °C)
Ambient air temperature for operation	-13...131 °F (-25...55 °C) - MID -13...140 °F (-25...60 °C) - NMI -13...140 °F (-25...60 °C) - IEC
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
Operating altitude	< 6561.68 ft (2000 m)
Color	White
9 mm pitches	14
Width	4.96 in (126 mm)
Height	4.06 in (103.2 mm)
Depth	2.73 in (69.3 mm)

## Ordering and shipping details

Category	09786 - SE ENTRY POWER METER
Discount Schedule	PL1
GTIN	3606480696428
Nbr. of units in pkg.	1
Package weight(Lbs)	23.99 oz (680 g)
Returnability	No
Country of origin	CN

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.35 in (8.5 cm)
Package 1 width	4.33 in (11 cm)
Package 1 Length	5.12 in (13 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	16
Package 2 Weight	407.90 oz (11564 g)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Unit Type of Package 3	P12
Number of Units in Package 3	384
Package 3 Weight	10107.09 oz (286536 g)
Package 3 Height	31.50 in (800 mm)
Package 3 width	47.24 in (1200 mm)
Package 3 Length	43.31 in (1100 mm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>