

Product data sheet

Characteristics

EZASHT100AC

shunt trip release SHT - 100..130 V AC - for
EZC400



Main

Range	EasyPact
Range of product	EZC100
Device short name	SHT
Product or component type	Voltage release
Device application	Control
Voltage release type	Shunt trip release
[Uc] control circuit voltage	100...130 V AC 50/60 Hz
Range compatibility	EasyPact EasyPact EZC

Complementary

Operating threshold	0.7 Un tripping
Response time	50 ms
Auxiliary connection terminal	Lead wire

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2 cm
Package 1 Width	9 cm
Package 1 Length	7.5 cm
Package 1 Weight	62 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	8 cm
Package 2 Width	10 cm
Package 2 Length	14 cm
Package 2 Weight	312 g
Unit Type of Package 3	S03
Number of Units in Package 3	120
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	8.201 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------