



## Main

Range	PowerPacT
Product name	PowerPacT B
Device short name	BD 015
Product or Component Type	Circuit breaker
Device Application	Distribution

## Complementary

Line Rated Current	15 A
Number of Poles	3P
Control type	Toggle
Breaking capacity code	D
Breaking capacity	25 KA 208Y/120 V AC 50/60 Hz UL 489 25 KA 240 V AC 50/60 Hz UL 489 18 KA 480/277 V AC 50/60 Hz UL 489 18 KA 480 V AC 50/60 Hz UL 489 14 KA 600Y/347 V AC 50/60 Hz UL 489 10 kA 250 V DC UL 489
[Ue] rated operational voltage	525 V AC 50/60 Hz UL 489
Network Frequency	50/60 Hz
[Ics] rated service breaking capacity	18 KA 220...240 V AC 50/60 Hz IEC 60947-2 18 KA 500...525 V AC 50/60 Hz IEC 60947-2 14 KA 380...415 V AC 50/60 Hz IEC 60947-2 14 kA 440 V AC 50/60 Hz IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV IEC 60947-2
Trip unit technology	Thermal-magnetic
Continuous current rating	80 %
[Ui] rated insulation voltage	800 V IEC 60947-2
Suitability for isolation	Yes IEC 60947-2
Utilisation category	Category A
Mechanical durability	20000 cycles IEC 947-1 Annex K ed 5.2
Electrical durability	10000 cycles IEC 947-1 Annex K ed 5.2 440 V In
Connection pitch	1.06 in (27 mm)
AWG gauge	AWG 6...AWG 2/0 fine stranded aluminium/copper AWG 14...AWG 3/0 rigid or stranded aluminium/copper
Local signalling	Presence of auxiliary contacts flag green)
Mounting mode	Clip-on 35 x 15 mm symmetrical DIN rail) By screws plate)
Electrical connection	Everlink lug line Everlink lug load
Tightening torque	44.25 Lbf.in (5 N.m) 0.00...0.02 in <sup>2</sup> (2.5...16 mm <sup>2</sup> ) (AWG 14...AWG 4) 79.66 lbf.in (9 N.m) 0.04...0.15 in <sup>2</sup> (25...95 mm <sup>2</sup> ) (AWG 3...AWG 3/0)
Number of slots	1 auxiliary switch OF plug-in) 1 voltage release MN or MX plug-in) 1 alarm switch SD plug-in)

Power wire stripping length	0.79 in (20 mm)
Color	Gray RAL 7016)
9 mm pitches	9
Height	5.39 in (137 mm)
Width	3.19 in (81 mm)
Depth	3.15 in (80 mm)
Net Weight	2.37 lb(US) (1.074 kg)
Quantity per Set	Set of 1
Circuit breaker application	HACR rated

## Environment

Quality labels	CE
Standards	CSA C22.2 No 5 GB 14048.2 NEMA AB1 NMX J-266 EN/IEC 60947-5-1 EN/IEC 60947-2 UL 489
Product certifications	UL IEC CCC EAC CSA NOM
IP degree of protection	Front cover IP40 IEC 60529
IK degree of protection	IK07 IEC 62262
Pollution degree	3 IEC 60947-1
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-58...185 °F (-50...85 °C)
Operating altitude	< 6561.68 ft (2000 m) without derating 5000 m with derating

## Ordering and shipping details



Category	01130-BD UNIT MOUNT BREAKER/SWITCH
Discount Schedule	DE2
GTIN	3606481152954
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	3.50 in (8.9 cm)
Package 1 Width	6.50 in (16.5 cm)
Package 1 Length	10.20 in (25.9 cm)
Package 1 Weight	3.09 lb(US) (1.4 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

RoHS exemption information	 Yes
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes
Halogen content performance	Halogen free product