

## Product data sheet

### Characteristics

# XY2CZ9310

## mounting kit - Ø 3.2 mm - L 10.5 m



### Main

|                                    |  |
|------------------------------------|--|
| Range of product                   | Telemecanique Emergency stop rope pull switches XY2C |
| Accessory / separate part type     | Mounting kit   |
| Accessory / separate part category | Mounting and fixing accessories                      |

### Complementary

|                                       |  |
|---------------------------------------|--|
| Product compatibility                 | XY2CJ<br>XY2CH   |
| Accessory / separate part destination | Emergency stop rope pull switch  |
| Kit composition                       | 1 x cable grip XY2CZ523<br>1 x end spring XY2CZ703<br>1 x galvanised cable |
| Cable outer diameter                  | 3.2 mm   |
| Cable length                          | 10.5 m   |
| Net weight                            | 0.444 kg   |

### Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 2.500 cm  |
| Package 1 Width              | 20.000 cm |
| Package 1 Length             | 20.000 cm |
| Package 1 Weight             | 413.000 g |
| Unit Type of Package 2       | S02       |
| Number of Units in Package 2 | 8         |
| Package 2 Height             | 15 cm     |
| Package 2 Width              | 30 cm     |
| Package 2 Length             | 40 cm     |
| Package 2 Weight             | 3.600 kg  |

### Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product                                      |
| REACH Regulation           | REACH Declaration  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free               | Yes  |
| RoHS exemption information | Yes  |
| Circularity Profile        | No need of specific recycling operations                   |

Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|