



## 環境

標準	EN/IEC 60204-1 UL 508 CSA C22.2 no 14 EN/IEC 60947-5-1 EN 1088/ISO 14119 EN/ISO 12100
產品認證	CSA[RETURN]cUL[RETURN]UL
防護處理	TC
運行環境空氣溫度	-25...70 °C
儲存環境溫度	-25...80 °C
抗振	6 gn (f= 10...55 Hz) 符合 IEC 60068-2-6
抗衝擊	50 gn 11 ms 符合 IEC 60068-2-27
電擊保護等級	等級II 符合 EN/IEC 61140
IP防護等級	IP67 conforming to EN/IEC 60529和EN/IEC 60947-5-1

## 包裝單位

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	20.0 cm
Package 1 Length	20.0 cm
Package 1 Weight	221.0 g
Unit Type of Package 2	P06
Number of Units in Package 2	160
Package 2 Height	80.0 cm
Package 2 Width	80.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	51.068 kg
Unit Type of Package 3	S03
Number of Units in Package 3	20
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	5.146 kg

## 供應的永續性

REACH 法規	 <a href="#">REACH 聲明</a>
EU RoHS 指令	預防性合規 (產品不在 EU RoHS 法規範圍內)  <a href="#">EU RoHS 聲明</a>
不含有毒重金屬	是
不含汞	是
RoHS 除外項目相關資訊	 <a href="#">是</a>

## 保固

保固	18 months
----	-----------