

Product data sheet

Characteristics

250SV46B

Transformer, buck boost, encapsulated,
0.25kVA, 1 phase, 120x240V primary, 16/32V
secondary, NEMA 3R, 80C rise

Main

Product	Buck and Boost Transformer
Enclosure Code	4A
Enclosure Type	NEMA 3R
Insulation Temperature	266 °F (130 °C)
Primary Voltage	120 x 240 V
Power Rating	0.25 kVA
Secondary Voltage	16/32 V
Temperature Rise	80 °C

Ordering and shipping details

Category	US10PE216265
Discount Schedule	0PE2
GTIN	785901019893
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.50 in (16.51 cm)
Package 1 Width	6.90 in (17.526 cm)
Package 1 Length	8.00 in (20.32 cm)
Package 1 Weight	9.520 lb(US) (4.318 kg)

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Take-back	No

Contractual warranty

Warranty

18 months
