



### Main

Range of product	Multi9
Product or Component Type	OC contact
Device short name	OFS
Signal contacts composition	1 C/O
Line Rated Current	AC-12 3 A at 380...415 V, AC 50/60 Hz AC-12 6 A at 220...240 V, AC 50/60 Hz DC-12 1 A at 130 V, DC DC-12 1.5 A at 60 V, DC DC-12 2 A at 48 V, DC DC-12 6 A at 24 V, DC
9 mm pitches	1

### Complementary

Mounting Mode	Fixed
Mounting Support	DIN rail
Comb busbar and distribution block compatibility	Top YES
Height	3.31 in (84 mm)
Width	0.35 in (9 mm)
Depth	2.87 in (73 mm)
Connections - terminals	Clamp terminal2 0.00 in <sup>2</sup> (1.5 mm <sup>2</sup> ) - flexible Clamp terminal2 0.00 in <sup>2</sup> (1.5 mm <sup>2</sup> ) - rigid Clamp terminal1 0.00...0.00 in <sup>2</sup> (0.5...2.5 mm <sup>2</sup> ) - flexible Clamp terminal1 0.00...0.00 in <sup>2</sup> (0.5...2.5 mm <sup>2</sup> ) - rigid
Wire stripping length	0.35 in (9 mm)
Tightening torque	8.85 lbf.in (1 N.m)

### Environment

Standards	EN/IEC 60947-5-1 EN 62019-2
Product Certifications	NEMKO[RETURN]DEMKO[RETURN]SEMKO[RETURN]CEBEC[RETURN]FIMKO
IP degree of protection	IP20 conforming to EN/IEC 60947-5-1
Pollution degree	3 EN/IEC 60947-5-1
Tropicalisation	2 EN/IEC 60947-5-1
Relative humidity	95 % 131 °F (55 °C)
Ambient air temperature for operation	-13...122 °F (-25...50 °C)
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)

### Ordering and shipping details

Category	US10DE201078
Discount Schedule	0DE2
GTIN	3303430269236
Returnability	No
Country of origin	ES

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.15 in (8 cm)
Package 1 Width	0.79 in (2 cm)
Package 1 Length	3.74 in (9.5 cm)
Package 1 Weight	1.52 oz (43 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	3.54 in (9 cm)
Package 2 Width	3.94 in (10 cm)
Package 2 Length	10.04 in (25.5 cm)
Package 2 Weight	20.60 oz (584 g)
Unit Type of Package 3	S03
Number of Units in Package 3	108
Package 3 Height	11.81 in (30 cm)
Package 3 Width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)
Package 3 Weight	12.55 lb(US) (5.694 kg)

## Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------