

8702SEO2V02S

NEMA Contactor, Type S, reversing, horizontal, Size 3, 90A, 50HP at 575VAC, 3 phase, up to 100kA, 3 pole, 120VAC coil, open style



Main

Product Type	Contactors
Product Range	Type S
Contactors Type	Reversing

Complementary

NEMA Size	3
Rated Current	90 A
Number of Poles	3P
Mounting Orientation	Horizontal
Wiring Mode	3 wires
Maximum Voltage Rating	600 V AC
Phase	3 phase
Horsepower Rating	25 HP 200 V AC 30 HP 230 V AC 50 HP 460 V AC 50 HP 575 V AC
SCCR	Circuit-breaker 150 A maximum, SCCR: 100 kA at 480 V AC Fuse J 200 A maximum, SCCR: 100 kA at 600 V AC Fuse T 200 A maximum, SCCR: 100 kA at 600 V AC Fuse RK1 200 A maximum, SCCR: 100 kA at 600 V AC Fuse RK5 200 A maximum, SCCR: 100 kA at 600 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	No control units
Pilot Light	No indicator
Other Equipment	Fuse not supplied
Terminal Type	Screw clamp terminals
Height	7.97 in (202.44 mm)
Width	12.72 in (323.09 mm)
Depth	7.00 in (177.80 mm)

Environment

Enclosure Type	Not rated (open device)
Certifications	UL Listed[RETURN]CSA

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	US10CP121273
Discount Schedule	0CP1
GTIN	785901808916
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.60 in (26.924 cm)
Package 1 Width	17.80 in (45.212 cm)
Package 1 Length	26.80 in (68.072 cm)
Package 1 Weight	17.00 lb(US) (7.711 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------