

9007MS05S0300

Limit switch, 9007ML, miniature, steel whisker wire, 10A at 240VAC, 1NO/1NC, 9 feet of cable, NEMA 4, 6, 6P, 12, 13



Main

| | |
|---------------------------|------------------------|
| Range of Product | 9007 |
| Series name | Miniature potted |
| Product or Component Type | Limit switch |
| Device short name | 9007MS/ML |
| Sensor design | Miniature |
| Body type | Fixed |
| Head type | Multi-directional head |
| Material | Metal |
| Body material | Cast zinc |
| Number of poles | 1 |

Complementary

| | |
|--|---|
| Fixing Mode | By the body |
| Movement of operating head | Multi-directional |
| Type of operator | Spring return wire whisker steel - |
| Type of approach | Multi-directional approach |
| Switch actuation | By any moving part |
| Contacts type and composition | NC-NO |
| Switch Function | SPDT |
| Contact form | Form C |
| Contacts material | Silver contacts |
| Contact operation | Snap action |
| Positive opening | Without |
| Electrical connection | Pre-wired cable bottom |
| Type of cable | SJTO AWG 18), 9 ft (2.7 m), Yellow |
| Terminals description ISO n°1 | (Black)Com (Red)NC (Green-yellow)Gnd (white)NO |
| Wire insulation material | PVC |
| Maximum force for tripping | 15 ozf |
| [Ie] rated operational current | 6 A 120 V AC, A300 NEMA rating designation 3 A 240 V AC, A300 NEMA rating designation 5 A 28 V DC |
| [Ithe] conventional enclosed thermal current | 10 A |
| [Ui] rated insulation voltage | 300 V 3)UL 508 300 V 3)CSA C22.2 No 14 |
| Electrical durability | 100000 cycles |
| Mechanical durability | 10000000 cycles |
| Marking | CSA UL CE |
| Sale per indivisible quantity | 1 |
| Height | 1.75 in (44.45 mm) |
| Width | 1.56 in (39.62 mm) |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

| | |
|------------|---------------------|
| Depth | 0.62 in (15.75 mm) |
| Net Weight | 1.2 lb(US) (0.5 kg) |

Environment

| | |
|---------------------------------------|--|
| Shock resistance | 35 gn 9 ms IEC 60068-2-27 |
| Vibration resistance | 10 gn 75...1200 Hz)IEC 60068-2-6 |
| NEMA degree of protection | NEMA 1 Nema type 250 NEMA 12 Nema type 250 NEMA 13 Nema type 250 |
| IP degree of protection | IP54 conforming to IEC 60529 |
| Ambient Air Temperature for Operation | -40.0000002...104.4 °C (-40...220 °F) |
| Ambient Air Temperature for Storage | -40.0000002...104.4 °C (-40...220 °F) |
| Protective treatment | Epoxy powder coat |
| Product Certifications | CSA[RETURN]CE[RETURN]UL |
| Standards | E78403 LR 25490 Class 32 11 03 |



Ordering and shipping details

| | |
|-------------------|--------------|
| Category | US10DS122431 |
| Discount Schedule | 0DS1 |
| GTIN | 785901319641 |
| Returnability | Yes |
| Country of origin | US |

Packing Units

| | |
|------------------------------|---------------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 2.4 in (6.1 cm) |
| Package 1 Width | 11.2 in (28.4 cm) |
| Package 1 Length | 11.9 in (30.2 cm) |
| Package 1 Weight | 20.000000000 oz (567.0 g) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free | Yes |
| RoHS exemption information |  Yes |
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|