

### Main

Range	Acti9
Device short name	MSC 18
Product or Component Type	Chassis
Device Application	Distribution

### Complementary

Range compatibility	Acti 9 Acti9 IsoBar B distribution board
Line Rated Current	250 A
Short-circuit withstand	25 kA 0.1 s
[I <sub>cw</sub> ] rated short-time withstand current	25 kA
Number of ways	1 way incomer) - 3P 18 ways outgoer)
Outgoer Pole capacity	18 x 0.71 in (18 mm)
Length	6.46 in (164 mm)
Width	8.46 in (215 mm)


### Ordering and shipping details

Category	US10DE200908
Discount Schedule	0DE2
GTIN	9321243001076
Returnability	No
Country of origin	US

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.74 in (9.5 cm)
Package 1 Width	9.45 in (24.0 cm)
Package 1 Length	17.72 in (45.0 cm)
Package 1 Weight	3.81 lb(US) (1.73 kg)

### Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------