



## Main

Range	Acti9
Product name	Acti9 iCV40
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Device short name	iCV40N
Device application	Distribution
Poles description	3P + N
Number of protected poles	3
Neutral position	Left
[In] rated current	25 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Earth-leakage sensitivity	30 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type AC
Breaking capacity	6000 A Icn at 400 V AC 50/60 Hz conforming to EN/IEC 61009-2-1
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Quality labels	EAC IMQ

## Complementary

Complementary	Outgoer
Network frequency	50/60 Hz
[Ue] rated operational voltage	400 V AC 50/60 Hz
Magnetic tripping limit	5...10 x In
Residual current tripping technology	Voltage independent
[Ics] rated service breaking capacity	6000 A 100 % x Icn at 400 V AC 50/60 Hz conforming to EN/IEC 61009-2-1
Rated breaking and making capacity	I <sub>dm</sub> 3000 A at 400 V AC 50/60 Hz conforming to EN/IEC 61009-2-1
Limitation class	3 conforming to EN/IEC 61009-2-1
[Ui] rated insulation voltage	440 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	4 kV
Contact position indicator	Yes
Control type	Toggle
Local signalling	Fault indication ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top or bottom: tooth
Connection pitch	18 Mm between phases 9 mm between phase and neutral
9 mm pitches	10
Height	93 mm

Width	90 mm
Depth	73 mm
Net weight	500 g
Colour	White
Mechanical durability	20000 cycles
Electrical durability	20000 cycles
Locking options description	Sealable Padlocking device
Connections - terminals	Tunnel type terminals top or bottom 1...16 mm <sup>2</sup> rigid Tunnel type terminals top or bottom 1...10 mm <sup>2</sup> flexible
Wire stripping length	14 mm for top or bottom connection
Tightening torque	2 N.m top or bottom
Earth-leakage protection	Integrated






## Environment

Standards	EN/IEC 61009-2-1
Product certifications	CE
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3
Overvoltage category	III conforming to IEC 60364
Electromagnetic compatibility	8/20 µs impulse withstand, 250 A conforming to EN/IEC 61009-1
Relative humidity	95 % at 55 °C
Operating altitude	2000 m
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-40...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.7 cm
Package 1 Width	11.4 cm
Package 1 Length	13.0 cm
Package 1 Weight	584.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	16
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	9.786 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts & cables product