



Main

Range	PowerPact
Product name	PowerPact L
Device short name	L-Frame
Product or Component Type	Circuit breaker
Device Application	Distribution

Complementary

Line Rated Current	400 A
Number of Poles	3P
Control Type	Toggle
Breaking capacity code	G
Breaking capacity	65 KA 240 V AC 50/60 Hz UL 489 35 KA 480 V AC 50/60 Hz UL 489 18 KA 600 V AC 50/60 Hz UL 489 20 KA 250 V DC UL 489 20 kA 500 V DC UL 489
[Ue] rated operational voltage	600 V AC 50/60 Hz IEC 60947-3
Network Frequency	50/60 Hz
[Ics] rated service breaking capacity	65 KA 220/240 V AC 50/60 Hz IEC 60947-2 35 KA 380/440/415 V AC 50/60 Hz IEC 60947-2 18 KA 500/525 V AC 50/60 Hz IEC 60947-2 20 KA 250 V DC IEC 60947-2 20 kA 500 V DC IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV IEC 60947-2
Trip unit technology	Electronic, ammeter, MicroLogic 6.3 A, LSIG
Continuous current rating	80 %
[Ui] rated insulation voltage	750 V IEC 60947-2
Trip unit name	MicroLogic 6.3 A
Protection technology	Current limiter
Suitability for isolation	Yes IEC 60947-2
Utilisation category	Category A
AWG gauge	2 x AWG 2/0...500 kcmil aluminium/copper
Local signalling	Ready 1 LED green) Alarm 1 LED 90 % Ir orange) Alarm LED 105 % Ir red) Switched off (OFF) 1 trip indicator green)
Mounting mode	Unit mount lug)
Mounting Support	Lug
Electrical connection	Terminal nut, line Lugs, load
Terminal identifier	AL600LS52K3
Long time pick-up adjustment range	0.25...1 x In
Tightening torque	442.5 lbf.in (50 N.m) 0.1...0.4 in ² (70...240 mm ²) (AWG 2/0...500 kcmil)

Number of slots	2 auxiliary switch OF plug-in 1 alarm switch SD plug-in 1 overcurrent trip switch SDE plug-in 1 voltage release MN or MX plug-in
Power wire stripping length	1.2 in (31 mm) 2.4 in (61 mm)
Color	Black
Height	13.4 in (340 mm)
Width	5.5 in (140 mm)
Depth	4.3 in (110 mm)
Net Weight	13.7 lb(US) (6.2 kg)
Communication interface	Modbus Ethernet
Circuit breaker application	HACR rated

Environment

Standards	UL CSA NEMA NOM-003-SCFI-2000 IEC 60947-2
Product certifications	UL[RETURN]CSA[RETURN]NOM
IP degree of protection	Front cover IP40
Pollution degree	3 IEC 60947-1
Ambient Air Temperature for Operation	-13.0000000000...158.0000000000 °F (-25...70 °C)
Ambient Air Temperature for Storage	-58.0000000000...185.0000000000 °F (-50...85 °C)
Operating altitude	< 6561.68 ft (2000 m) without derating 5000 m with derating

Ordering and shipping details

Category	US10DE201116
Discount Schedule	0DE2
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.750 in (22.225 cm)
Package 1 Width	10.750 in (27.305 cm)
Package 1 Length	19.50 in (49.53 cm)
Package 1 Weight	15.0003 lb(US) (6.804 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	"WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov "
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------
