



Main

| | |
|-------------------------------------|--|
| Range | TeSys TeSys Deca |
| Product name | TeSys LRD TeSys Deca |
| Product or Component Type | Non differential thermal overload relay |
| Device short name | LR3D |
| Relay application | Motor protection |
| Product Compatibility | LC1D50A LC1D65A |
| Network type | DC AC |
| Thermal overload class | Class 10A IEC 60947-4-1 |
| Thermal protection adjustment range | 48...65 A |
| [Ui] rated insulation voltage | Power circuit 600 V CSA Power circuit 600 V UL Power circuit 690 V IEC 60947-4-1 |

Complementary

| | |
|--|---|
| Network Frequency | 0...400 Hz |
| Mounting support | Plate, with specific accessories Rail, with specific accessories Under contactor |
| Tripping threshold | 1.14 +/- 0.06 I _r IEC 60947-4-1 |
| Auxiliary contact composition | 1 NO + 1 NC |
| [I _{th}] conventional free air thermal current | 5 A signalling circuit |
| Permissible current | 0.95 A 380 V AC-15 signalling circuit 0.06 A 440 V DC-13 signalling circuit |
| [U _e] rated operational voltage | 690 V AC 0...400 Hz power circuit IEC 60947-4-1 |
| Associated fuse rating | 4 A gG for signalling circuit 4 A BS for signalling circuit |
| [U _{imp}] rated impulse withstand voltage | 6 kV |
| Phase failure sensitivity | Tripping current 130 % of I _r on two phase, the last one at 0 |
| Control type | Red push-button stop Blue push-button reset |
| Temperature compensation | -4...140 °F (-20...60 °C) |
| Connections - terminals | Control circuit screw clamp terminals 2 0.00...0.00 in ² (1...2.5 mm ²) flexible without cable end Control circuit screw clamp terminals 2 0.00...0.00 in ² (1...2.5 mm ²) flexible with cable end Control circuit screw clamp terminals 2 0.00...0.00 in ² (1...2.5 mm ²) solid without cable end Power circuit EverLink BTR screw connectors 1 0.00...0.05 in ² (1...35 mm ²) flexible without cable end Power circuit EverLink BTR screw connectors 1 0.00...0.05 in ² (1...35 mm ²) flexible with cable end Power circuit EverLink BTR screw connectors 1 0.00...0.05 in ² (1...35 mm ²) solid without cable end |
| Tightening torque | Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Power circuit 44.25 lbf.in (5 N.m) EverLink BTR screw connectors |
| Height | 2.76 in (70 mm) |
| Width | 2.17 in (55 mm) |

| | |
|------------|------------------------|
| Depth | 4.84 in (123 mm) |
| Net Weight | 0.83 lb(US) (0.375 kg) |

Environment

| | |
|---------------------------------------|--|
| Climatic withstand | IACS E10 |
| IP degree of protection | IP20 conforming to IEC 60529 |
| Ambient air temperature for operation | -4...140 °F (-20...60 °C) without derating IEC 60947-4-1 |
| Ambient Air Temperature for Storage | -76...158 °F (-60...70 °C) |
| Flame retardance | V1 conforming to UL 94 |
| Mechanical robustness | Shocks15 Gn for 11 ms IEC 60068-2-7 Vibrations4 gn IEC 60068-2-6 |
| Dielectric strength | 1.89 kV 50 Hz IEC 60947-1 |
| Standards | EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 GB/T 14048.4 GB/T 14048.5 |
| Product Certifications | IEC[RETURN]UL[RETURN]CSA[RETURN]CCC[RETURN]EAC[RETURN]DNV-GL[RETURN]RMRS[RETURN]EU-RO MR[RETURN]LROS (Lloyds register of shipping)[RETURN]UKCA |





Ordering and shipping details



| | |
|-------------------|---------------|
| Category | US10I1222347 |
| Discount Schedule | 0I12 |
| GTIN | 3389119215930 |
| Returnability | Yes |
| Country of origin | US |

Packing Units

| | |
|------------------------------|-------------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 2.56 in (6.5 cm) |
| Package 1 Width | 4.33 in (11.0 cm) |
| Package 1 Length | 5.51 in (14.0 cm) |
| Package 1 Weight | 13.86 oz (393.0 g) |
| Unit Type of Package 2 | S02 |
| Number of Units in Package 2 | 13 |
| Package 2 Height | 5.91 in (15 cm) |
| Package 2 Width | 11.81 in (30 cm) |
| Package 2 Length | 15.75 in (40 cm) |
| Package 2 Weight | 12.12 lb(US) (5.496 kg) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation |  REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |

| | |
|--------------------------|--|
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile |  End Of Life Information |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|