

LTMR08PBD

Motor Management, TeSys T, motor controller,
Profibus DP, 6 logic inputs, 3 relay logic
outputs, 0.4 to 8A, 24VDC



Main

Range	TeSys
Product name	TeSys T
Device short name	LTMR
Product or Component Type	Motor controller
Device Application	Equipment monitoring and control
Measurement current	0.4...8 A
[Us] rated supply voltage	24 V DC
Current Consumption	56...127 mA
Supply voltage limits	20.4...26.24 V DC
Communication Port Protocol	Profibus DP
Bus type	Profibus DP polarised 2-wire RS485 1...125 9.6 kbit/s...12 Mbit/s, SUB-D 9 2 shielded twisted pairs, type A Profibus DP polarised 2-wire RS485 1...125 9.6 kbit/s...12 Mbit/s, terminal block 2 shielded twisted pairs, type A

Complementary

[Ui] rated insulation voltage	690 V EN/IEC 60947-1 690 V CSA C22.2 No 14 690 V UL 508
[Uimp] rated impulse withstand voltage	6 kV current or voltage measurement circuit EN/IEC 60947-4-1 0.8 kV communication circuit EN/IEC 60947-4-1 0.8 kV supply, inputs and outputs EN/IEC 60947-4-1
Short-circuit withstand	100 kA conforming to EN/IEC 60947-4-1
Associated fuse rating	4 A gG output 0.5 A gG control circuit
Protection Type	Thermal protection Load fluctuation Power factor variation Phase failure Overload Reverse polarity protection Overload (long time) Earth-leakage protection Locked rotor Thermal overload protection Phase unbalance
Network and machine diagnosis type	Motor control command recording Running hours counter/operating time Trip history information Fault recording Starting current and time Phase fault and earth fault trip counters Remaining operating time before overload tripping Waiting time after overload tripping Trip context information Event recording
Logic input number	6
Input current	7 mA
Current state 0 guaranteed	Logic input < 5 V <= 15 mA 5 ms

Current state 1 guaranteed	Logic input < 15 V 2...15 mA 15 ms
Maximum output switching frequency	2 Hz
Load current	5 A 250 V AC logic output 5 A 30 V DC logic output
Permissible power	480 VA AC-15), I _e = 2 A, 500000 cycles output) 30 W DC-13), I _e = 1.25 A, 500000 cycles output)
Maximum operating rate	1800 cyc/h
Contacts type and composition	1 NO + 1 NC fault signal 3 NO
Metering type	Earth-fault current Average current I _{avg} Imbalance current Phase current I ₁ , I ₂ , I ₃ RMS Temperature
Measurement accuracy	5...15 % earth fault current internal measurement 1 % voltage 100...830 V) 3 % power factor 5 % earth fault current external measurement +/- 30 min/year internal clock 0,02 Temperature 1 % current 5 % active and reactive power
Overvoltage category	III
Connection pitch	0.20 in (5.08 mm)
Connections - terminals	Control circuit connector 1 0.00...0.00 in ² (0.25...2.5 mm ²) AWG 24...AWG 14)flexible with cable end Control circuit connector 1 0.00...0.00 in ² (0.2...2.5 mm ²) AWG 24...AWG 14)flexible without cable end Control circuit connector 1 0.00...0.00 in ² (0.25...2.5 mm ²) AWG 24...AWG 14)flexible without cable end Control circuit connector 1 0.00...0.00 in ² (0.2...2.5 mm ²) AWG 24...AWG 14)solid without cable end Control circuit connector 2 0.00...0.00 in ² (0.2...1 mm ²) AWG 24...AWG 14)flexible with cable end Control circuit connector 2 0.00...0.00 in ² (0.2...1.5 mm ²) AWG 24...AWG 14)flexible without cable end Control circuit connector 2 0.00...0.00 in ² (0.5...1.5 mm ²) AWG 24...AWG 14)flexible without cable end Control circuit connector 2 0.00...0.00 in ² (0.2...1 mm ²) AWG 24...AWG 14)solid without cable end
Tightening torque	Control circuit 4.43...5.31 lbf.in (0.5...0.6 N.m) flat 0.12 in (3 mm)
Pollution degree	3
Electromagnetic compatibility	Electrostatic discharge, 3, 8 kV air, 6 kV contact, conforming to EN/IEC 61000-4-2 Radiated RF fields, 3, 10 V/m, conforming to EN/IEC 61000-4-3 Fast transients immunity test (other circuits), level 3, 2 kV, conforming to EN/IEC 61000-4-4 Fast transients immunity test (on supply and relay outputs), level 4, 4 kV, conforming to EN/IEC 61000-4-4 Voltage dips and interruptions immunity test, 70 %, 500 ms, conforming to EN/IEC 61000-4-11 Conducted RF disturbances, 10 V, conforming to EN/IEC 61000-4-6 Temperature sensor: surges (serial mode), 0.5 kV, conforming to EN/IEC 61000-4-5 Temperature sensor: surges (common mode), 1 kV, conforming to EN/IEC 61000-4-5 Control circuit: surges (serial mode), 1 kV, conforming to EN/IEC 61000-4-5 Control circuit: surges (common mode), 1 kV, conforming to EN/IEC 61000-4-5 Communication: surges (common mode), 2 kV, conforming to EN/IEC 61000-4-5 Relay outputs and supply: surges (serial mode), 2 kV, conforming to EN/IEC 61000-4-5 Relay outputs and supply: surges (common mode), 4 kV, conforming to EN/IEC 61000-4-5
Width	3.58 in (91 mm)
Height	2.40 in (61 mm)
Depth	4.82 in (122.5 mm)
Net Weight	1.17 lb(US) (0.53 kg)
Web services	Web server
Compatibility code	LTMR

Environment

Standards	IACS E10 EN 60947-4-1 IEC 60947-4-1 UL 508 CSA C22.2 No 14
Product Certifications	ATEX[RETURN]GL[RETURN]LROS (Lloyds register of shipping)[RETURN]CSA[RETURN]UL[RETURN]C-tick[RETURN]CCC[RETURN]DNV[RETURN]RINA[RETURN]ABS[RETURN]KERI[RETURN]EA
Protective treatment	12 x 24 hour cycles EN/IEC 60068-2-30 48 h EN/IEC 60070-2-11 TH EN/IEC 60068
Fire resistance	1202 °F (650 °C) EN/IEC 60695-2-12 1760 °F (960 °C) UL 94
Ambient air temperature for operation	-4...140 °F (-20...60 °C)
Ambient Air Temperature for Storage	-40...176 °F (-40...80 °C)
Operating altitude	<= 6561.68 ft (2000 m) without derating
Mechanical robustness	Vibrations mounted on symmetrical rail1 Gn, 5...300 Hz EN/IEC 60068-2-6 Vibrations plate mounted4 Gn, 5...300 Hz EN/IEC 60068-2-6 Shocks half sine wave acceleration15 Gn for 11 ms EN/IEC 60068-2-27
IP Degree of Protection	IP20

Ordering and shipping details

Category	US10I1222338
Discount Schedule	0I12
GTIN	3389119404808
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.83 in (7.2 cm)
Package 1 Width	3.94 in (10.0 cm)
Package 1 Length	5.35 in (13.6 cm)
Package 1 Weight	18.20 oz (516.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	10
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	12.13 lb(US) (5.5 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------