



Main

Range of product	ARGUS standard movement detector
Range	ARGUS
Product or component type	Presence detector with IR receiver
Load type	Motor: : 100 W Relay: : 5 A - 250 V LED lighting: : 400 W Incandescent lamps: : 2300 W - 230 V Halogen lamp: : 1200 W - 230 V Halogen lamp with standard electronic transformer: 1200 VA Halogen lamp with standard ferromagnetic transformer: 1200 VA Fluorescent tube: 1200 VA, 140 µF Compact fluorescent lamp: : 400 W
Colour tint	White

Complementary

Network frequency	50/60 Hz
Input function	Switch External trigger
Output voltage	220...250 V
Output current	10 A
Number of channels	2
Control type	Movement sensor
Function available	Switching, toggling, dimming
Light intensity adjustment	10...2000 lux
Horizontal detection angle	360 °
Mounting height	2.5 m

Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.2 cm
Package 1 Width	11.7 cm
Package 1 Length	17.7 cm
Package 1 Weight	462 g
Unit Type of Package 2	S03
Number of Units in Package 2	8
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.336 kg
Unit Type of Package 3	P12
Number of Units in Package 3	64
Package 3 Height	50 cm
Package 3 Width	80 cm

Package 3 Length	120 cm
Package 3 Weight	53.544 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins