



Main

Product line	QO
Product type	Bar

Complementary

Number of connectors	7
Wire size	AWG 14...AWG 4 copper AWG 12...AWG 4 aluminium
Provided equipment	2 screw
Bar length	2.87 in (73 mm)
Maximum length of segment	1.26 in (32 mm)
Device mounting	Direct mounting back of enclosure
Height	0.437 in (11.10 mm)
Depth	0.312 in (7.92 mm)
Tightening torque	30 lb.in Mounting screw 30 lb.in 20 lb.in, AWG 14...AWG 10, copper 20 lb.in, AWG 12...AWG 10, aluminium 35 lb.in, AWG 6...AWG 4 25 lb.in, AWG 8 25 lb.in, AWG 14...AWG 12, copper 25 lb.in, AWG 12...AWG 10, aluminium

Ordering and shipping details

Category	US1DE3A00102
Discount Schedule	DE3A
GTIN	785901026372
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.40 in (1.016 cm)
Package 1 Width	1.20 in (3.048 cm)
Package 1 Length	5.00 in (12.7 cm)
Package 1 Weight	1.60 oz (45.359 g)
Unit Type of Package 2	PAL
Number of Units in Package 2	2160
Package 2 Height	26.50 in (67.31 cm)

Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	260.00 lb(US) (117.934 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------