



Main

| | |
|---------------------------|---|
| Range of product | ARGUS standard movement detector |
| Range | ARGUS |
| Product or component type | Movement detector |
| Load type | Incandescent lamp: 1000 W, AC Low voltage halogen lamp with wire-wound transformer: 500 VA Low voltage halogen lamp with electronic transformer: 250 VA Fluorescent tube: 200 VA, AC Compact fluorescent lamp: 3 x 23 W, AC Capacitive: : 6 A, 21 µF, AC Capacitive: : 10 A, 14 µF, AC Halogen lamp: 900 W, AC |
| Colour tint | White |
| Type of packing | Carton |

Complementary

| | |
|--------------------------------|---|
| [Ue] rated operational voltage | 220...240 V |
| Network frequency | 50 Hz |
| [Ue] rated operational voltage | 220...240 V |
| Output current | 10 A |
| Type of setting | Light sensitivity adjustable Time adjustment |
| Time delay | 3 s...30 min |
| Light intensity adjustment | 5...2000 lux |
| Horizontal detection angle | 0...120 ° |
| Detection range | Frontal: 12 m |
| Material | PC (polycarbonate) matt |
| Device mounting | Surface |
| Mounting height | 2.5 m |

Environment

| | |
|---------------------------------------|-------------|
| IP degree of protection | IP55 |
| Ambient air temperature for operation | -15...40 °C |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 9.2 cm |
| Package 1 Width | 17.2 cm |
| Package 1 Length | 9.8 cm |
| Package 1 Weight | 343 g |
| Unit Type of Package 2 | S04 |
| Number of Units in Package 2 | 36 |
| Package 2 Height | 30 cm |
| Package 2 Width | 40 cm |
| Package 2 Length | 60 cm |
| Package 2 Weight | 13.294 kg |

| | |
|------------------------------|------------|
| Unit Type of Package 3 | P12 |
| Number of Units in Package 3 | 432 |
| Package 3 Height | 105 cm |
| Package 3 Width | 80 cm |
| Package 3 Length | 120 cm |
| Package 3 Weight | 171.528 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|