

Main

Range of Product	Hyde Park
Sensor Type	Ultrasonic sensor transmitter
Series name	Standard format
Device short name	SM451
Sensor design	Miniature
Material	Plastic
[Us] rated supply voltage	12...24 V DC
Electrical connection	1 connector pin 4 pins
[Sd] sensing range	0.335 ft (0.102 m)
IP degree of protection	IP66

Complementary

[Sn] nominal sensing distance	0.335 ft (0.102 m)
Type of sensing window	Fixed
Condition of use	Thru beam
Transmission frequency	500 kHz

Ordering and shipping details

Category	US10DS222490
Discount Schedule	0DS2
GTIN	03389119091480
Returnability	No

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
SCIP Number	435317c3-e86a-47b7-acde-88c832f96adb
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Take-back	No

Contractual warranty

Warranty	18 months
----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.