

# LVS03285

Front Plate, PrismaSeT G, Cut-out type,  
for ComPact NSX630 vertical fixed, 15M,  
enclosure W600mm



## Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure
Type of front plate	Cut-out
Installed device	ComPact: fixed INV400 - control: direct front rotary handle - vertical installation ComPact: fixed NSX400 without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX400 with earth leakage protection - control: toggle - vertical installation
Poles description	1 x 4P: mounting plate support: INV400 vertical installation 1 x 4P: mounting plate support: NSX400 vertical installation
Operating position	Superposed

## Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
Number of vertical modules [50 mm]	15
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASTA
Surface finish	Textured Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	750 mm
Width	600 mm
Net weight	2.6 kg
Quantity per set	Set of 1
Functional unit	600 mm PrismaSeT G floor-standing enclosure ComPact INV400 fixed direct front rotary handle vertical 4P 1 direct 600 mm PrismaSeT G wall-mounted enclosure ComPact INV400 fixed direct front rotary handle vertical 4P 1 direct 600 mm PrismaSeT G floor-standing enclosure ComPact NSX400 without fixed toggle vertical 4P 1 direct 600 mm PrismaSeT G wall-mounted enclosure ComPact NSX400 without fixed toggle vertical 4P 1 direct 600 mm PrismaSeT G floor-standing enclosure ComPact NSX400 with fixed toggle vertical 4P 1 direct 17 600 mm PrismaSeT G wall-mounted enclosure ComPact NSX400 with fixed toggle vertical 4P 1 direct 17

## Environment

IP degree of protection	IP30
-------------------------	------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.800 cm
Package 1 Width	51.500 cm
Package 1 Length	76.200 cm
Package 1 Weight	2.679 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	4
Package 2 Height	19.000 cm
Package 2 Width	53.500 cm
Package 2 Length	82.200 cm
Package 2 Weight	11.680 kg
Unit Type of Package 3	P12
Number of Units in Package 3	24
Package 3 Height	53.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	81.500 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product