

# LVS03417

Mounting plate, PrismaSeT P, for NSX100/  
INV250/UA/BA controller, horizontal, C/O, mot  
mech, W650mm



## Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle
Installation description	Cubicle - width 650 mm depth 400 mm Cubicle - width 650 mm depth 600 mm
Installed device	Source changeover: fixed BA controller - horizontal installation Source changeover: fixed NSX100...250 source changeover - control: remote control - horizontal installation Source changeover: fixed UA controller - horizontal installation
Poles description	2 x 3P: fixed NSX100...250 source changeover horizontal installation 2 x 4P: fixed NSX100...250 source changeover horizontal installation
Number of vertical modules [50 mm]	4 module(s): BA controller, direct in 650 mm Widecubicle 8 module(s): NSX100...250 source changeover, direct in 650 mm Widecubicle 4 module(s): UA controller, direct in 650 mm Widecubicle
Standards	IEC 61439-2
Product certifications	ASTA

## Complementary

Material	Sheet steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Matt Textured
Colour	White (RAL 9003)
Width	650 mm
Height	200 mm
Net weight	3 kg
Functional unit	650 mm 600 mm PrismaSeT P cubicle source changeover BA controller fixed horizontal 1 direct 4 12.5 mm 650 mm 400 mm PrismaSeT P cubicle source changeover NSX100...250 source changeover fixed remote control horizontal 3P 2 direct 8 12.5 mm 650 mm 400 mm PrismaSeT P cubicle source changeover NSX100...250 source changeover fixed remote control horizontal 4P 2 direct 8 12.5 mm 650 mm 600 mm PrismaSeT P cubicle source changeover UA controller fixed horizontal 1 direct 4 12.5 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	11.000 cm
Package 1 Length	58.000 cm
Package 1 Weight	2.930 kg
Unit Type of Package 2	S04
Number of Units in Package 2	8
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	24.159 kg
Unit Type of Package 3	P12
Number of Units in Package 3	32
Package 3 Height	43.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	108.500 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations