

LVS03690

Front plate, PrismaSeT P, for NS630b to NS1600, 7M, W650, vertica, fixed, with cut-out, white, RAL 9003



Main

| | |
|------------------------------------|--|
| Range | PrismaSeT |
| Range of product | PrismaSeT P |
| Product or component type | Front plate |
| Accessory / separate part category | Installation accessory |
| Range compatibility | PrismaSeT PrismaSeT P cubicle |
| Type of front plate | Cut-out |
| Installed device | ComPact: fixed NS1250 - control: toggle - vertical installation ComPact: fixed NS1250 - control: direct front rotary handle - vertical installation ComPact: fixed NS1600 - control: toggle - vertical installation ComPact: fixed NS1600 - control: direct front rotary handle - vertical installation ComPact: fixed NS630b...1000 - control: toggle - vertical installation ComPact: fixed NS630b...1000 - control: direct front rotary handle - vertical installation |
| Poles description | 1 x 3P: mounting plate support: NS1250 vertical installation 1 x 4P: mounting plate support: NS1250 vertical installation 1 x 3P: mounting plate support: NS1600 vertical installation 1 x 4P: mounting plate support: NS1600 vertical installation 1 x 3P: mounting plate support: NS630b...1000 vertical installation 1 x 4P: mounting plate support: NS630b...1000 vertical installation |
| Operating position | Vertical |

Complementary

| | |
|------------------------------------|--|
| Enclosure/cubicle description | Cubicle - width 650 mm depth 400 mm Cubicle - width 650 mm depth 800 mm |
| Connection position | Front connection Rear connection |
| Number of vertical modules [50 mm] | 7 |
| Standards | IEC 61439-2 IEC 61439-1 |
| Product certifications | ASTA |
| Material | Steel |
| Surface finish | Matt Textured |
| Protective treatment | Electrophoresis treatment and hot-polymerised polyester epoxy powder |
| Colour | White (RAL 9003) |
| Height | 350 mm |
| Width | 500 mm |
| Net weight | 1.8 kg |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

| | |
|------------------------------|------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 5.000 cm |
| Package 1 Width | 35.000 cm |
| Package 1 Length | 50.000 cm |
| Package 1 Weight | 1.794 kg |
| Unit Type of Package 2 | S04 |
| Number of Units in Package 2 | 5 |
| Package 2 Height | 30.000 cm |
| Package 2 Width | 40.000 cm |
| Package 2 Length | 60.000 cm |
| Package 2 Weight | 9.944 kg |
| Unit Type of Package 3 | P12 |
| Number of Units in Package 3 | 40 |
| Package 3 Height | 73.000 cm |
| Package 3 Width | 80.000 cm |
| Package 3 Length | 120.000 cm |
| Package 3 Weight | 87.500 kg |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |