

LVS03691

Front plate, PrismaSeT P, for NS-MTZ1/NT,
8M, W650, withdrawable device, with cut-out,
white, RAL 9003



Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle
Type of front plate	Cut-out
Installed device	<p>ComPact: drawout NS1250 - control: toggle - vertical installation</p> <p>ComPact: drawout NS1250 - control: direct front rotary handle - vertical installation</p> <p>ComPact: drawout NS1250 - control: motor mechanism - vertical installation</p> <p>ComPact: drawout NS1600 - control: toggle - vertical installation</p> <p>ComPact: drawout NS1600 - control: direct front rotary handle - vertical installation</p> <p>ComPact: drawout NS1600 - control: motor mechanism - vertical installation</p> <p>ComPact: drawout NS630b...1000 - control: toggle - vertical installation</p> <p>ComPact: drawout NS630b...1000 - control: direct front rotary handle - vertical installation</p> <p>ComPact: drawout NS630b...1000 - control: motor mechanism - vertical installation</p> <p>Masterpact: drawout NT06...10 - control: toggle - vertical installation</p> <p>Masterpact: drawout NT06...10 - control: motor mechanism - vertical installation</p> <p>Masterpact: drawout NT12 - control: toggle - vertical installation</p> <p>Masterpact: drawout NT12 - control: motor mechanism - vertical installation</p> <p>Masterpact: drawout NT16 - control: toggle - vertical installation</p> <p>Masterpact: drawout NT16 - control: motor mechanism - vertical installation</p>
Poles description	<p>1 x 3P: mounting plate support: NS1250 vertical installation</p> <p>1 x 4P: mounting plate support: NS1250 vertical installation</p> <p>1 x 3P: mounting plate support: NS1600 vertical installation</p> <p>1 x 4P: mounting plate support: NS1600 vertical installation</p> <p>1 x 3P: mounting plate support: NS630b...1000 vertical installation</p> <p>1 x 4P: mounting plate support: NS630b...1000 vertical installation</p> <p>1 x 3P: mounting plate support: NT06...10 vertical installation</p> <p>1 x 4P: mounting plate support: NT06...10 vertical installation</p> <p>1 x 3P: mounting plate support: NT12 vertical installation</p> <p>1 x 4P: mounting plate support: NT12 vertical installation</p> <p>1 x 3P: mounting plate support: NT16 vertical installation</p> <p>1 x 4P: mounting plate support: NT16 vertical installation</p>
Operating position	<p>Vertical</p> <p>Horizontal</p>

Complementary

Enclosure/cubicle description	Cubicle - width 650 mm depth 400 mm Cubicle - width 650 mm depth 800 mm
Connection position	Front connection Rear connection
Number of vertical modules [50 mm]	8
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA
Material	Steel
Surface finish	Matt Textured
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	400 mm
Width	500 mm
Net weight	1.8 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.800 cm
Package 1 Width	40.000 cm
Package 1 Length	50.000 cm
Package 1 Weight	1.800 kg
Unit Type of Package 2	S04
Number of Units in Package 2	5
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	9.977 kg
Unit Type of Package 3	P12
Number of Units in Package 3	40
Package 3 Height	74.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	91.500 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations