



### Main

Range	Linergy
Range of product	Linergy
Product or component type	Connection
Product name	Linergy BW
Product name	PrismaSeT PrismaSeT G enclosure PrismaSeT PrismaSeT P enclosure Linergy Linergy BW busbar
Accessory / separate part category	Current distribution accessory
Standards	IEC 61439-1, inside enclosure IEC 61439-2, inside enclosure
Product certifications	ASTA

### Complementary

Cubicle-device connection	Linergy BW universal power supply block
Poles description	4P
Installation description	Cubicle duct - width 300 mm Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm
Installed device	ComPact: fixed INS250 - control: direct front rotary handle vertical installation ComPact: fixed INV250 - control: direct front rotary handle vertical installation EasyPact: fixed CVS100...160 without earth leakage protection - control: direct front rotary handle vertical installation EasyPact: fixed CVS250 without earth leakage protection - control: direct front rotary handle vertical installation EasyPact: fixed CVS100...160 without earth leakage protection - control: toggle vertical installation EasyPact: fixed CVS250 without earth leakage protection - control: toggle vertical installation ComPact: fixed INV100 - control: direct front rotary handle vertical installation ComPact: fixed NSX100...160 without earth leakage protection - control: toggle vertical installation ComPact: fixed NSX250 without earth leakage protection - control: toggle vertical installation ComPact: fixed NSX100...160 without earth leakage protection - control: direct front rotary handle vertical installation ComPact: fixed NSX250 without earth leakage protection - control: direct front rotary handle vertical installation ComPact: fixed INV200 - control: direct front rotary handle vertical installation ComPact: fixed INV160 - control: direct front rotary handle vertical installation
[Ie] rated operational current	250 A
Colour	Anthracite grey (RAL 7016)
Net weight	2.72 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.





## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	28.0 cm
Package 1 Length	38.5 cm
Package 1 Weight	2.726 kg
Unit Type of Package 2	P12
Number of Units in Package 2	18
Package 2 Height	24.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	60.5 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations