



## Main

Range	Linergy
Range of product	Linergy
Product or component type	Busbar
Product name	Linergy BS
Range compatibility	PrismaSeT PrismaSeT P enclosure
Busbar description	Flat bar
Quantity per set	Set of 1

## Complementary

Installation direction	Vertical, operating position: lateral Horizontal, operating position: top Horizontal, operating position: bottom
Installation description	Cubicle - width 650 mm Cubicle - width 650 + 150 mm Cubicle duct - width 300 mm Cubicle duct - width 400 mm
[Ie] rated operational current	1880 A at 35 °C
[Icw] rated short-time withstand current	60 KA (1 s) for 2 supports (horizontal position) 85 KA (1 s) for 3 supports (horizontal position) 40 KA (1 s) (horizontal position) 85 KA (1 s) for 2 supports (horizontal position) 50 kA (1 s) (horizontal position)
Permissible current	1880 A at 35 °C: ≤ IP31 1670 A at 35 °C: > IP31
Busbar cross section	120 x 10 mm
Length	2000 mm
Width	120 mm
Depth	10 mm
Net weight	21.9 kg
Colour	Natural
Type of busbar connection	Without hole

## Environment

Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	18.0 cm
Package 1 Length	212.0 cm
Package 1 Weight	21.694 kg
Unit Type of Package 2	PAL

Number of Units in Package 2	18
Package 2 Height	20.0 cm
Package 2 Width	18.0 cm
Package 2 Length	212.0 cm
Package 2 Weight	412.0 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product