



Main

Range	PowerLogic
Product name	CT
Product or component type	Current transformer
Secondary current	5 A
Accuracy class	Class 0.5 at 8 VA Class 1 at 10 VA
[In] rated current	300 A

Complementary

Current transformer type	Tropicalised for busbar and cable
Current transformer ratio	300/5
[Ith] conventional free air thermal current	18 kA
Dynamic withstand current	2.5 Ith
Maximum safety factor	5
[Ue] rated operational voltage	< 720 V AC 50/60 Hz
[Ui] rated insulation voltage	3 kV
Mounting mode	Insulated locking screw By screws Clip-on
Mounting support	DIN rail Busbar Mounting plate
Width	Outside: 56 mm
Height	Outside: 80 mm
Depth	Frame : 43 mm Total : 63 mm
Diameter	27 mm
Net weight	0.303 kg
[Uimp] rated impulse withstand voltage	3 kV
Electrical insulation class	Class B
Cable outer diameter	27 mm
Opening of bars	32.5 x 10.5 25.5 x 15.5
Sealing	Without

Environment

Standards	VDE 0414 IEC 61869-2
Product certifications	EAC[RETURN]CE
IP degree of protection	IP20
Relative humidity	0...95 %
Ambient air temperature for operation	-25...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.200 cm
Package 1 Width	7.000 cm
Package 1 Length	9.000 cm
Package 1 Weight	313.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	36
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	11.710 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins