



Main

Range of product	Unica
Device application	Power supply
Product or component type	Switched socket
Device presentation	Mechanism with fixing frame
Outlet poles configuration	2P + E
Outlet standard deviation	European

Complementary

Device mounting	Flush
Mounting support	Wall mounted
Socket number	2
Pilot light	Red neon indicator
Rated current	13 A
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50 Hz
Load type	Resistive
Number of modules	4 modules
Fixing mode	By screw M3.5
Fixing center	120.6 mm
Colour tint	Aluminium
Contacts material	Brass and phosphor bronze
Connections - terminals	Pillar terminal
Terminal identifier	N Earth L
Tightening torque	0.4 N.m
Clamping connection capacity	2 x 4 mm ² for rigid cable(s) 2 x 4 mm ² for stranded cable(s) 2 x 4 mm ² for flexible cable(s) 3 x 2.5 mm ² for rigid cable(s) 3 x 2.5 mm ² for stranded cable(s) 3 x 2.5 mm ² for flexible cable(s)
Material	PC (polycarbonate): grid plate PC (polycarbonate): base
Projecting depth	8 mm
Quantity per set	Set of 10
Type of packing	Polybag
Embedding depth	35 mm
Depth	15 mm
Width	140 mm
Height	83 mm
Net weight	0.12 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company Schneider Electric. This information is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.






Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
IK degree of protection	IK01
IP degree of protection	IP20
Standards	BS 1363 BS 7671 SASO 2203
Environmental characteristic	Indoor use

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	11.7 cm
Package 1 Length	22.3 cm
Package 1 Weight	119 g
Unit Type of Package 2	CAR
Number of Units in Package 2	5
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	625 g
Unit Type of Package 3	P12
Number of Units in Package 3	1000
Package 3 Height	120 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	157000 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations